

SCALANCE XF204-2BA DNA Managed IE Y switch, 4 x 10/100 Mbit/s, 2 x bus adapter interfaces, Error signaling contact, set button, redundant 24 V DC power supply, PROFINET device, Extended temperature range -40°C...+70°C, Conformal Coating, with electron. manual on DVD, C-plug optional, supplied without bus adapter



Product type designation	SCALANCE XF204-2BA DNA
Product options	XF-200 base device without mounted BusAdapter
Transfer rate	
Transfer rate	10 Mbit/s, 100 Mbit/s
Interfaces / for communication / Integrated	
Number of electrical connections	
<ul style="list-style-type: none"> for network components or terminal equipment 	0
Interfaces / other	
Number of electrical connections	
<ul style="list-style-type: none"> for signaling contact 	1
<ul style="list-style-type: none"> for power supply 	1
<ul style="list-style-type: none"> for redundant voltage supply 	1
Type of electrical connection	
<ul style="list-style-type: none"> for signaling contact 	2-pole terminal block
<ul style="list-style-type: none"> for power supply 	2-pole terminal block
design of the removable storage	
<ul style="list-style-type: none"> C-PLUG 	Yes

Signal inputs/outputs	
Operating voltage / of the signaling contacts	
<ul style="list-style-type: none"> at DC / Rated value 	24 V
Operating current / of the signaling contacts	
<ul style="list-style-type: none"> at DC / maximum 	0.1 A
Supply voltage, current consumption, power loss	
Type of voltage / of the supply voltage	DC
Supply voltage	
<ul style="list-style-type: none"> external 	24 V
<ul style="list-style-type: none"> external / minimum 	19.2 V
<ul style="list-style-type: none"> external / maximum 	28.8 V
Product component / fusing at power supply input	Yes
Fuse protection type / at input for supply voltage	2.5 A (cannot be changed by user)
Consumed current / maximum	0.36 A
Power loss [W]	
<ul style="list-style-type: none"> at DC / at 24 V 	8.6 W
Ambient conditions	
Ambient temperature	
<ul style="list-style-type: none"> during operation 	-40 ... +70 °C
<ul style="list-style-type: none"> during storage 	-40 ... +85 °C
<ul style="list-style-type: none"> during transport 	-40 ... +85 °C
Relative humidity	
<ul style="list-style-type: none"> at 25 °C / without condensation / during operation / maximum 	95 %
Protection class IP	IP20
Design, dimensions and weights	
Design	compact
Width	100 mm
Height	117 mm
Depth	74 mm
Net weight	0.25 kg
Mounting type	
<ul style="list-style-type: none"> 35 mm DIN rail mounting 	Yes
<ul style="list-style-type: none"> wall mounting 	No
<ul style="list-style-type: none"> S7-300 rail mounting 	No
<ul style="list-style-type: none"> S7-1500 rail mounting 	No
Product features, product functions, product components / general	
Cascading in the case of a redundant ring / at reconfiguration time of $\sim 0.3\text{ s}$	50
Cascading in cases of star topology	any (depending only on signal propagation time)
Product functions / management, configuration, engineering	

Product function	
• CLI	Yes
• web-based management	Yes
• MIB support	Yes
• TRAPs via email	Yes
• Configuration with STEP 7	Yes
• Port mirroring	Yes
• multiport mirroring	Yes
• PROFINET IO diagnosis	Yes
PROFINET conformity class	B
Product function / switch-managed	Yes
Protocol / is supported	
• Telnet	Yes
• HTTP	Yes
• HTTPS	Yes
• TFTP	Yes
• FTP	No
• BOOTP	No
• DCP	Yes
• LLDP	Yes
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes
Identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 – higher-level designation/location designation	Yes

Product functions / Diagnostics

Product function	
• Port diagnostics	Yes
• Statistics Packet Size	Yes
• Statistics packet type	Yes
• Error statistics	Yes

Product functions / DHCP

Product function	
• DHCP client	Yes

Product functions / redundancy

Product function	
• of the PROFINET IO device / is supported / PROFINET system redundancy (S2)	Yes
• Ring redundancy	Yes

<ul style="list-style-type: none"> • High Speed Redundancy Protocol (HRP) 	Yes
<ul style="list-style-type: none"> • high speed redundancy protocol (HRP) with redundancy manager 	Yes
<ul style="list-style-type: none"> • high speed redundancy protocol (HRP) with standby redundancy 	Yes

Protocol / is supported / Media Redundancy Protocol (MRP)	Yes
---	-----

Product function	
<ul style="list-style-type: none"> • media redundancy protocol (MRP) with redundancy manager 	Yes
<ul style="list-style-type: none"> • Media Redundancy Protocol for Planned Duplication (MRPD) 	No
<ul style="list-style-type: none"> • of the PROFINET IO device / is supported / H-Sync forwarding 	Yes
<ul style="list-style-type: none"> • Parallel Redundancy Protocol (PRP)/operation in the PRP-network 	No
<ul style="list-style-type: none"> • Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA) 	No
<ul style="list-style-type: none"> • Passive listening 	Yes

Product functions / Security

Protocol / is supported	
<ul style="list-style-type: none"> • SSH 	Yes

Product functions / time

Product function	
<ul style="list-style-type: none"> • SICLOCK support 	No
Protocol / is supported	
<ul style="list-style-type: none"> • NTP 	No
<ul style="list-style-type: none"> • SNTP 	Yes

System modification during operation

Product function / configuration in RUN via CiR/H-CiR	Yes
---	-----

Standards, specifications, approvals

Standard	
<ul style="list-style-type: none"> • for FM 	FM3611: Class 1, Divison 2, Group A, B, C, D / T4, CL.1, Zone 2, GP. IIC, T4
<ul style="list-style-type: none"> • for hazardous zone 	EN 60079-0 : 2006, EN 60079-15: 2005, II 3 G Ex nA II T4 KEMA 07 ATEX 0145X
<ul style="list-style-type: none"> • for safety / from CSA and UL 	UL 61010-2-201
<ul style="list-style-type: none"> • for hazardous zone / from CSA and UL 	ANSI / ISA 12.12.01, CSA C22.2 No. 213-M1987, CL. 1 / Div. 2 / GP. A, B, C, D T4, CL. 1 / Zone 2 / GP. IIC, T4
<ul style="list-style-type: none"> • for emitted interference 	EN 61000-6-4:2001 (Class A)
<ul style="list-style-type: none"> • for interference immunity 	EN 61000-6-2, EN 61000-6-4

Security for industrial automation and control systems / acc. to IEC 62443-4-2:2019	Yes
---	-----

Standards, specifications, approvals / CE

Certificate of suitability / CE marking	Yes
---	-----

Standards, specifications, approvals / other

Certificate of suitability	EN 61000-6-2, EN 61000-6-4
• C-Tick	Yes
• Railway application in accordance with EN 50155	No
• Railway application in accordance with EN 50124-1	No
• KC approval	Yes

Standards, specifications, approvals / marine classification

Marine classification association	
• Bureau Veritas (BV)	Yes
• Korean Register of Shipping (KRS)	Yes

accessories

Product extension / optional / C-PLUG	Yes
---------------------------------------	-----

Further information / Internet-Links

Internet-Link	
• to website: Selector SIMATIC NET SELECTION TOOL	http://www.siemens.com/snst
• to website: Industrial communication	http://www.siemens.com/simatic-net
• to website: Industry Mall	https://mall.industry.siemens.com
• to website: Information and Download Center	http://www.siemens.com/industry/infocenter
• to website: Image database	http://automation.siemens.com/bilddb
• to website: CAx Download Manager	http://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com

Security information

Security information

Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action (e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit <http://www.siemens.com/industrialsecurity>. To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit <http://support.automation.siemens.com>. (V3.4)

last modified:

05/13/2020