



USB 3.0 never looked this good.

Kingston's DataTraveler® Mini 3.0 features a compact form factor that makes it the ideal companion for devices in which the USB ports are close together. It fits on a key ring or in a pocket to keep it accessible.

This capless drive is available in multiple colors and includes a key loop and metal casing to protect the drive from drops, bumps and knocks. It's backwards compatible with existing USB 2.0 ports, allowing 2.0 users to migrate to 3.0 in the future without replacing their drive.

DataTraveler Mini 3.0 is backed by a five-year warranty, free technical support and legendary Kingston® reliability.

- > Small form factor
- > Stylish metal casing
- > Fashionable colors
- > Customizable with your logo and/or digital files

DataTraveler Mini 3.0



16GB	
READ 70MB/s*	WRITE 10MB/s*

*Based on Internal Testing

32GB – 64GB	
READ 70MB/s*	WRITE 15MB/s*

*Based on Internal Testing

Features/specs on reverse >>

DataTraveler Mini 3.0

FEATURES/BENEFITS

- > **Versatile** — mini size makes it perfect for use in USB ports with limited space
- > **Convenient** — small, capless and pocket-sized for easy transportability
- > **Stylish** — durable metal casing with built-in key loop
- > **Customizable**¹ — Customize Kingston DataTraveler USB Flash drives by adding your logo and/or digital files to increase your organization's brand recognition. The Customization Program offers unique packaging, custom profiles, color adjustments, content loading and more, all with easy and convenient ordering

SPECIFICATIONS

- > **Capacities**² 16GB, 32GB, 64GB
- > **Speed**³ 16GB — 70MB/s read, 10MB/s write
32GB, 64GB — 70MB/s read, 15MB/s write
- > **Dimensions** 42.33mm x 12.66mm x 5.98mm
- > **Operating Temperature** 0°C to 60°C
- > **Storage Temperature** -20°C to 85°C
- > **Warranty/support** 5-year warranty with free technical support



HIGH-CAPACITY FILES
PHOTOS MUSIC
STORAGE
HIGH-SPEED FILES
USB 3.0 FLASH DRIVE



COMPATIBILITY TABLE

Operating System	USB 3.0 ⁴	USB 2.0
Windows® 8.1	✓	✓
Windows 8	✓	✓
Windows 8 RT	✓	✓
Windows 7 (SP1)	✓	✓
Windows Vista® (SP1, SP2)	✓	✓
Windows XP (SP3)	✓	✓
Mac OS X v.10.6.x+	✓	✓
Linux v.2.6.x+	✓	✓

KINGSTON PART NUMBERS

DTM30/16GB — Red
DTM30/32GB — Cyan
DTM30/64GB — Grey

¹ Minimum quantity required. Performed at the factory.

² Some of the listed capacity on a Flash storage device is used for formatting and other functions and thus is not available for data storage. As such, the actual available capacity for data storage is less than what is listed on the products. For more information, go to Kingston's Flash Memory Guide at kingston.com/flashguide.

³ Speed may vary due to host hardware, software and usage.

⁴ Requires a host device with a USB 3.0 port

THIS DOCUMENT SUBJECT TO CHANGE WITHOUT NOTICE

©2013 Kingston Technology Corporation, 17600 Newhope Street, Fountain Valley, CA 92708 USA. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. MKD-271US

