





## 156503-2 Product Details



**156503-2**

TE Internal Number: 156503-2



### Multiple Circuit Housings with Tabs & Receptacles



Always EU RoHS/ELV Compliant (Statement of Compliance)

#### Product Highlights:

- Contact
- Contact Type = Receptacle
- Mating Area Interface Dimensions = 6.35 x 0.80 mm
- Wire Range = 4.00-6.00<sup>2</sup> [11-10] mm [AWG]
- Insulation Diameter = 3.70-5.20 [.094-.205] mm [in]

[View all Features](#)

#### Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)



[Request Sample](#)



[Find Similar Products](#)



[Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [250 SERIES FASTIN - FASTON RECEPTACLE](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Related Products:

- [Tooling](#)

[List all Documents](#)

Feedback

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Product Type](#) = Contact
- [Receptacle Style](#) = Straight
- [Wire/Cable Type](#) = Regular Wire
- [Finish](#) = Tin
- [Insertion Force](#) = Normal
- [Insulation Support](#) = With
- FASTON = Yes

#### Termination Features:

- [Crimp Type](#) = F-Crimp

#### Dimensions:

- [Mating Area Interface Dimensions](#) (mm [in]) = 6.35 x 0.80 [.250 x .031]
- [Insulation Diameter](#) (mm [in]) = 3.70-5.20 [.094-.205]

#### Body Features:

- [Wire Range](#) (mm [AWG]) = 4.00-6.00<sup>2</sup> [11-10]
- [Material](#) = Brass

#### Contact Features:

- Contact Type = Receptacle

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant
- UL Rating = Recognized
- CSA Certified = Yes

#### Packaging Features:

- [Packaging Method](#) = Strip

#### Other:

- Line = FASTIN-FASTON .250
- Brand = AMP

### Corporate Information

[About TE](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

### Quick Links

[Distributor Inventory](#)

[Product Cross Reference](#)

[Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

### Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Knowledge Base](#)

[Manage Your Account](#)

### Keep Me Informed



[Terms & Conditions](#)

[Privacy Policy](#)

[AODA Accessibility Policy](#)

[AODA Multi-Year Accessibility  
Plan](#)