

PRODUCT DATASHEET

ECO AREA L SPD 60W 827 6600LM GR

ECO AREA LOW POWER | Straightforward road and path lighting luminaires



Areas of application

- Road lighting
- Streets
- Car parks
- Area lighting

Product benefits

- Functional and minimalistic design
- Low maintenance and operation costs due to long lifetime of LED
- 5 years guarantee

Product features

- Asymmetric light distribution for various application areas
- Robust die-cast aluminum housing
- Side-entry mounting for 48...60 mm poles
- Surge protection: up to 10 kV (L/N-PE)
- Integrated wide voltage driver, suitable for 100 - 240 V_{AC}
- Pre-installed, flexible 0.5 m cable (H05RN-F), wrapped 3 x 1.0 mm² single wires



TECHNICAL DATA**Electrical data**


Nominal wattage	60.00 W
Nominal voltage	100...240 V
Mains frequency	50...60 Hz
Nominal current	270 mA
Inrush current	20 A
Inrush current time T_{H50}	200 μ s
Max. no. of lum. on circuit break. B16 A	16
Max. no. of lum. on circuit break. C10 A	15
Max. no. of lum. on circuit break. C16 A	24
Power factor λ	> 0.90
Total harmonic distortion	< 20 %
Protection class	I
Operating mode	Mains voltage

Photometrical data

Luminous flux	6600 lm
Luminous efficacy	110 lm/W
Color temperature	2700 K
Light color (designation)	Warm White
Color rendering index Ra	> 80
Standard deviation of color matching	≤ 5 sdc _m
Photobiological safety group acc. to EN62778	RG1
Photobiological safety group acc. to EN62471	RG1
Beam angle	135 ° x 75 °

Dimensions & Weight

Length	409.00 mm
Width	151.00 mm
Height	83.00 mm
Product weight	1554.00 g
Cable length	500 mm



Materials & Colors

Product color	Gray
Housing color	Gray
Body material	Aluminum
Cover material	Polycarbonate (PC)
Light emitting surface material	Polycarbonate (PC)
Mercury content	0.0 mg

Application & Mounting

Ambient temperature range	-30...+50 °C
Temperature range at storage	-35...+70 °C
Type of connection	Cable, 3-pole
Type of protection	IP66
Protection class IK (shock resistance)	IK08
Dimmable	No
Mounting type	Side entry
Mounting location	Pole
LED module replaceable	Not replaceable

Lifespan






Lifespan L70/B50 at 25 °C	50000 h
Number of switching cycles	100000

Certificates & Standards

Standards	CE / EAC
Luminaire with limited surface temperature, "D sign"	No

DOWNLOAD DATA

DOWNLOAD DATA

	User instruction ECO CLASS AREALIGHTING
	Tender documents Tender Text 4058075425217
	Declarations of conformity CE Declaration of Conformity_ECO CLASS AREA
	IES file (IES) ECO AREA L SPD 60W 827 6600LM GR
	LDT file (Eulumdat) ECO AREA L SPD 60W 827 6600LM GR

LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075425217	Folding box 1	448 mm x 121 mm x 200 mm	1754.00 g	10.84 dm ³
4058075425224	Shipping box 8	507 mm x 467 mm x 422 mm	14840.00 g	99.92 dm ³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

References / Links

– For Guarantee see www.ledvance.com/guarantee

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.