




Part Number : [2213910002](#)
Product Description : 7.50mm Pitch Lever
Activated Fixed Mount PCB Terminal Block,
35° Wire Entry, Bussed Terminals, 2 Circuits
Series Number : 221391
Status : Active
Product Category : Terminal Blocks and
Barrier Strip
Engineering Number : MX-TLM-405A-02



Documents & Resources

Drawings

[2213910002_sd.pdf](#)

3D Models and Design Files

[2213910002_stp.zip](#)

Specifications

[1302270418-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Terminal Blocks and Barrier Strip
Series	221391
Description	7.50mm Pitch Lever Activated Fixed Mount PCB Terminal Block, 35° Wire Entry, Bussed Terminals, 2 Circuits
Application	Wire-to-Board
Component Type	One Piece
Product Name	Lever Activated Fixed Mount
Type	PCB Terminal Blocks and Connectors
UPC	196823120657

Electrical

Current - Maximum per Contact	40.0A
Voltage - Maximum	300V

Physical

Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Green
Entry Angle	35° Angle
Lock to Mating Part	None
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyamide

Net Weight	4.400/kg
Number of Rows	1
Orientation	Vertical
Panel Mount	No
PC Tail Length	3.60mm
PCB Thickness - Recommended	2.00mm
Pitch - Mating Interface	7.50mm
Pitch - Termination Interface	7.50mm
Polarized to Mating Part	N/A
Stackable	No
Temperature Range - Operating	-40° to +115°C
Termination Interface Style	Through Hole
Wire Size (AWG)	8, 10, 12, 14, 16, 18, 20, 22, 24
Wire Size mm ²	0.38-3.73