



APC Smart-UPS, Line Interactive, 2200VA, Rackmount 2U, 230V, 8x IEC C13+2x IEC C19 outlets, Network Card, AVR, LCD

SMT2200RMI2UNC

## **Overview**

Presentation	Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Lead time	Usually in Stock
NA - :	

#### Main

Product or component type Uninterruptible power supply (UPS)

## **Batteries & Runtime**

Run Time	View Runtime Graph ☐
Efficiency	View Efficiency Graph ☐
Battery type	Lead-acid battery
Additional information	Configurable for 220 : 230 or 240 nominal output voltage
Extended runtime	0
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	3 h
Number of battery replacement quantity	1
Battery life	35 year(s)
Replacement battery	RBC43 ☐
Battery charger power	169 W rated

## **General**

Provided equipment	CD with software Documentation CD Installation guide Rack mounting hardware Rack mounting support rails Smart UPS signalling RS-232 cable Temperature probe USB cable	
Number of power module	0	
Number of power module filled slots	0	
Number of power module free slots	0	
product web sub-family	Network card pre-installed	

Rates duty January 2016

Redundant	No	
Physical		
Number of rack unit	2U	
Cable length	2.00 m	
Number of cables	1	
Height	8.6 cm	
Width	48 cm	
Depth	68.3 cm	
Net weight	42.22 kg	
Mounting location	Front	
Mounting preference	Lower	
Mounting mode	Rack-mounted	
Two post mountable	0	
USB compatible	No	
Input		
Main Input Voltage	230 V	
Other Input Voltage	220 V 240 V	
Input Connection Type	BS1363A British IEC 320 C20 Schuko CEE 7 / EU1-16P	
Input voltage limits	151302 V adjustable 160286 V	
Network frequency	50/60 Hz +/- 3 Hz auto-sensing	
Output		
Output		
Main Output Voltage	230 V	
Other Output Voltage	220 V 240 V	
Rated power in W	1980 W	
rated power in VA	2200 VA	
output connection type	8 IEC 320 C13 3 IEC Jumpers 1 IEC 320 C19	
Maximum configurable power in VA	2200 VA	
Maximum configurable power in W	1980 W	
Transfer time	4 ms typical : 8 ms maximum	
UPS type	Line interactive	
Wave type	Sine wave	

# Conformance

Output frequency

50/60 Hz +/- 3 Hz sync to mains

Product certifications	CE	
	EAC	
	IRAM	
	RCM	
	VDE	
	UK PSTI	
Marking	GS Mark	
Standards	EN/IEC 62040-1:2019/A11:2021	
	EN/IEC 62040-2:2006/AC:2006	
	EN/IEC 62040-2:2018	

## **Environmental**

Acoustic level	55 dBA	
Heat dissipation	215 Btu/h	
Operating altitude	010000 ft	
Ambient air temperature for operation	040 °C	
Ambient air temperature for storage	-1545 °C	
Storage altitude	0.000000000015240.000000000 m	
Relative humidity	095 %	
Storage Relative Humidity	095 %	

# **Communications & Management**

control panel	Multifunction LCD status and control console	
Emergency power off	Optional	
Preinstalled device	Network management card 3 with environmental monitoring	
Control panel	LED status display with on line : on battery : replace battery and overload indicators	
Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays	

# **Surge Protection and Filtering**

Surge energy rate 375 J

# **Packing Units**

_	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	25.4 cm
Package 1 Width	98 cm
Package 1 Length	60 cm
Package 1 Weight	49.63 kg

## **Contractual warranty**

Warranty 3 years repair or replace (excluding battery) and 2 years for battery



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	3327
Environmental Disclosure	Product Environmental Profile

### **Use Better**

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	0637234b-27c7-4e32-ae29-543dd4803a99
REACh Regulation	REACh Declaration
Optimized Energy Efficiency	Energy efficient product

### **Use Again**

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Removable battery	User replaceable
Take-back	Yes