

Main

Range of product	Odace
Product or component type	Electronic bell
Device presentation	Mechanism with fixing frame
Type of packing	Paint cover




Complementary

Device mounting	Flush
Provided equipment	Supplied with claws
Fixing mode	By claws By screws
Technology type	Electronic
Colour tint	White (RAL 9003)
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC 50/60 Hz
Acoustic level	70 dB/1m
Signalling type	5 melodies
Protection type	Fuse protection
Associated fuse rating	10 A
Connected auxiliaries	3 indicator lights connected in parallel 10 standard push-buttons connected in parallel
Number of terminals	5 screw terminals
Shape of screw head	Pozidriv No 1
Clamping connection capacity	1 x 1.5 mm ² for rigid cable(s) 1 x 1.5 mm ² for stranded cable(s) 1 x 1.5 mm ² for flexible cable(s)
Wire stripping length	12 mm
Material	Thermoplastic ABS-UV stabilised: centre plate PBT (polybutylene terephthalate) GF30: support frame PA (polyamide) 6 GF20 FR: casing
Height	71 mm
Width	71 mm
Depth	49 mm
Embedding depth	33 mm
Net weight	0.13 kg
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...35 °C
Standards	2006/95/EC 2004/108/EC IEC 62080
IK degree of protection	IK04
IP degree of protection	IP21D
Environmental characteristic	Window-cleaning fluid UV resistant Oil Petrol Bleach Alcohol Acetone Liquid soap

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes