



FAG

6052-M-C3

Deep groove ball bearing

Deep groove ball bearing 60...-M, single row, solid brass cage

Technical information



Your current product variant

Sealing	Without	Not sealed
Cage	M	Solid brass cage, rolling element guided
Tolerance class	PN	Normal (PN)
Dimensional / heat stabilization	S1	Rings dimensional stabilized up to 200°
Lubricant	Without	Bearing not greased
Radial internal clearance	C3 (Group 3)	Internal clearance larger than CN
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	260 mm	Bore diameter
D	400 mm	Outside diameter
B	65 mm	Width
C _r	310,000 N	Basic dynamic load rating, radial
C _{0r}	405,000 N	Basic static load rating, radial
C _{ur}	14,300 N	Fatigue load limit, radial
n _G	2,750 1/min	Limiting speed
n _{gr}	2,250 1/min	Reference speed
≈m	29.8 kg	Weight



Mounting dimensions

d _{a min}	274.6 mm	Minimum diameter shaft shoulder
D _{a max}	385.4 mm	Maximum diameter of housing shoulder
r _{a max}	3 mm	Maximum fillet radius

Dimensions

r _{min}	4 mm	Minimum chamfer dimension
D ₁	357.5 mm	Shoulder diameter outer ring
d ₁	304.05 mm	Shoulder diameter inner ring

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	200 °C	Operating temperature max.

Calculation factors

f ₀	15.7	Calculation factor
----------------	------	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Grease Lubrication
	Oil Lubrication
	Not sealed
	Large bearing