

Protective conductor terminal with quick-connect technology Cross-section: 0.5-2.5 mm<sup>2</sup>, Width: 6.2mm, Color: green-yellow



Model	
Product brand name	ALPHA
General technical data	
Insulation material	thermoplastic
Terminal contact spacing	6.2 mm
Protection class	
Combustibility class acc. to UL 94	V0
Appearance	
Color	green-yellow
Product details	
Product feature / PEN function	No
Product component / required / connection plate	No
Number	
Number of terminal levels	1
Number of terminal points / per terminal level	2
Connections	

Connectable conductor cross-section / solid	
<ul style="list-style-type: none"> <li>• minimum</li> <li>• maximum</li> </ul>	0.5 mm <sup>2</sup> 2.5 mm <sup>2</sup>
Connectable conductor cross-section / stranded	
<ul style="list-style-type: none"> <li>• minimum</li> <li>• maximum</li> </ul>	0.5 mm <sup>2</sup> 2.5 mm <sup>2</sup>
Connectable conductor cross-section / finely stranded	
<ul style="list-style-type: none"> <li>• with core end processing / minimum</li> <li>• with core end processing / maximum</li> <li>• without core end processing / minimum</li> <li>• without core end processing / maximum</li> </ul>	0.5 mm <sup>2</sup> 2.5 mm <sup>2</sup> 2.5 mm <sup>2</sup> 2.5 mm <sup>2</sup>
Type of electrical connection	
<ul style="list-style-type: none"> <li>• 1</li> <li>• 2</li> </ul>	insulation piercing connection insulation piercing connection
Position / of the terminal	top

### Mechanical Design

Height / with lowest-profile installation	39.3 mm
Length	62.6 mm
Mounting type	DIN rail 35 mm
Net weight	13 g
Material / of the insulating body	Thermoplastic

### Environmental conditions

Ambient temperature / during operation	
<ul style="list-style-type: none"> <li>• minimum</li> <li>• maximum</li> </ul>	-25 °C 35 °C

### Certificates

Reference code	
<ul style="list-style-type: none"> <li>• acc. to DIN EN 61346-2</li> <li>• acc. to DIN EN 81346-2</li> </ul>	X X

<b>General Product Approval</b>	<b>Declaration of Con- formity</b>	<b>other</b>
---------------------------------	--	--------------



[Miscellaneous](#)

### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8WH3000-0CF07>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/8WH3000-0CF07>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8WH3000-0CF07](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8WH3000-0CF07)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>