

8569-01

## Torque wrench DREMOMETER

750-2000 Nm

Code ETIM  
**7695410** EC002132

EAN UNSPSC  
**4002805856918** 27-11-17-15

Country of origin eCl@ss  
**Germany** 21-04-02-22

Customs tariff number  
**82041100**



## Article description

- Use:
- Controlled screw tightening in the range of 750 - 2000 Nm
- For use in almost all industrial manufacturing areas
- Features:
- Classified according to DIN EN ISO 6789-2:2017 Type II Class A, incl. traceable test certificate, calibrated to a maximum permissible deviation of +/- 3 % and thus more precise than the +/- 4 % required by the standard
- 1" square drive with pin-locking mechanism DIN 3120 - B 25, ISO 1174
- Automatic short-path actuation with tactile impulse and audible signal
- Single scale with a scale graduation of 50 Nm
- Technical advantage/Function:
- Lightweight yet robust (as the housing is made of an aluminium alloy) and resilient, very workshop-friendly
- No inaccuracies whether used with both hands or held away from the handle (as for standard torque wrenches)
- Both the square drive and fulcrum are on an axis which ensures a high degree of user safety; can be extended to reduce the user's working load.
- Extremely low wear attributable to reduced forces in a lever mechanism
- Forged lever chain from our group own quality forge
- Maximum precision even when subjected to extreme continuous use
- Long life cycles and tool lives • Easy operation - fast and safe torque tightening
- Easy adjustment thanks to attractive adjusting button secured against loss at the end of the handle
- Single- and double-square drive for controlled bi-directional tightening

## Article parts list

Extension tube ,8564-92 ,8572-74

## Article information

Contents (Qty of pieces)	1	Trigger mechanism	Short path triggering
Net weight [kg]	12 kg	Precision +/-	+/- 3 %
Total length [mm]	932 mm	Direction of tightening	Left and right
Total width [mm]	60 mm	Fixed setting	no
Total height [mm]	71 mm	Test certificate	DIN EN ISO 6789-2:2017
Material	Aluminum alloy	Head height 1 [mm]	40 mm
Standard	DIN 3120 - B 25 ISO 1174	Width of head 1 [mm]	60,0 mm
Drive connector square (male)	1"	Torque wrench type	EL
Drive connector square (male)	25 mm	Calibration length	2213 mm
Drive type/drive	Double square rigid	Graduation [n·m]	50 Nm
Torque (min.) [N·m]	750 Nm	Distance housing - square drive	30 mm
Torque (max.) [N·m]	2000 Nm	Storage/Content	Box
Torque range (min./max.) [N·m]	750 Nm - 2000 Nm	Length of extension tube 1	925 mm
Torque range (min./max.) [lbf·ft]	-	Length of slip-on tube 2	745 mm