




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Tab**

Wire Size: **1 – 2.5 mm<sup>2</sup>**

Mating Tab Width: **2.8 mm [.11 in]**

Mating Tab Thickness: **.8 mm [.031 in]**

## Features

### Configuration Features

|                                   |               |
|-----------------------------------|---------------|
| Compatible With Wire & Cable Type | Discrete Wire |
| Connection Capacity               | Single        |

### Contact Features

|                                |                |
|--------------------------------|----------------|
| Quick Disconnect Terminal Type | Tab            |
| Mating Tab Width               | 2.8 mm[.11 in] |
| Mating Tab Thickness           | .8 mm[.031 in] |
| Terminal Orientation           | Straight       |
| Terminal Plating Material      | Silver         |
| Crimp Type                     | F-Crimp        |

### Termination Features

|                       |              |
|-----------------------|--------------|
| Product Terminates To | Wire & Cable |
|-----------------------|--------------|

### Mechanical Attachment

|                         |                |
|-------------------------|----------------|
| Locking Lance Height    | 1.2 mm[.05 in] |
| Wire Insulation Support | With           |

### Dimensions



|                                      |                              |
|--------------------------------------|------------------------------|
| Product Length                       | 21.1 mm[.83 in]              |
| Compatible Insulation Diameter Range | 1.8 – 2.9 mm[.071 – .144 in] |
| Terminal Material Thickness          | .38 mm[.015 in]              |
| Wire Size                            | 1 – 2.5 mm <sup>2</sup>      |

### Usage Conditions

|                   |             |
|-------------------|-------------|
| Insulation Option | Uninsulated |
|-------------------|-------------|

### Packaging Features

|                    |        |
|--------------------|--------|
| Packaging Quantity | 3500   |
| Packaging Method   | Carton |

### Other

|      |             |
|------|-------------|
| Line | FASTON .110 |
|------|-------------|

## Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

|   |   |
|---|---|
| EU RoHS Directive 2011/65/EU                  | Compliant   |
| EU ELV Directive 2000/53/EC                   | Compliant   |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold   |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JUL 2017 (174)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free   |
| Solder Process Capability                     | Not applicable for solder process capability  |

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


### Also in the Series | FASTIN-FASTON 110




Automotive Housings(6)



Automotive Signal & Power Connector Housings(6)



Automotive Terminals(5)




Crimp Terminal Housings(34)




Quick Disconnects(78)


### Customers Also Bought




TE Part #CC2644-000  
B-106-8502CS100




TE Part #CC2628-000  
B-106-3631CS100




TE Part #CC2641-000  
B-106-3632CS100



TE Part #CC2645-000  
D-406-0003CS50



TE Part #CC2630-000  
B-106-4631CS100



TE Part #CC2643-000  
B-106-7502CS100




TE Part #CC2637-000  
B-106-1802CS100



TE Part #CC2621-000  
B-106-1501CS100



TE Part #CC2649-000  
B-106-1803CS50



TE Part #CC2631-000  
B-106-7401CS100



## Documents

### CAD Files

#### 3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_928994-1\\_E.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_928994-1\\_E.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_928994-1\\_E.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Product Specifications

#### Application Specification

German

#### Application Specification

English

#### Application Specification

English