

ELECTRIC SUBMERSIBLE PUMPS

SIP SUB 1040-FS ITEM NO: 06863

SIP SUB 1075-FS Dirty Water ITEM NO: 06867

SIP SUB 1100-SS Dirty Water ITEM NO: 06869

A new generation of submersible water pumps, with some units suitable for both clean and dirty water. These are designed to be super heavy-duty, and to meet the demands of a variety of domestic and commercial water pumping needs.

Key Features:

- Operating depth of up to 8 metres
- Float switch protects from running dry
- Super heavy-duty plastic housing, or stainless steel casing for 06869
- Compact and lightweight design



06869



06863



06867

NOTE: NOT SUITABLE FOR PERMANENT INSTALLATION

FLOAT SWITCH

230 V SUPPLY

MODEL	SIP SUB 1040-FS	SIP SUB 1075-FS DIRTY WATER	SIP SUB 1100-SS DIRTY WATER
PRODUCT CODE	06863	06867	06869
Input Supply	230 V (13 A)	230 V (13 A)	230 V (13 A)
Motor	400 W (0.5 HP)	750 W (1 HP)	1000 W (1.3 HP)
Water Flow Rate	150 Ltr/min	225 Ltr/min	242 Ltr/min
Maximum Pumping Head	8 metres	8 metres	11 metres
Maximum Operating Depth	7 metres	7 metres	8 metres
Maximum Particle Diameter	5 mm	35 mm	35 mm
Outlet Diameter	25 to 40 mm Ø 1" BSP	25 to 40 mm Ø 1" BSP	25 to 40 mm Ø 1" BSP
Float Switch	✓	✓	✓
Cable Length	10 metres	10 metres	10 metres
Maximum Water Temperature	35°C	35°C	35°C
Protection	IPX8	IPX8	IPX8
Weight	4.2 kg	5.3 kg	6.6 kg
Packaged Dimensions	341 x 212 x 162 mm	358 x 212 x 162 mm	354 x 215 x 176 mm
Barcode Number	5012713068630	5012713068678	5012713068692

SPECIFICATIONS