



005111 - SUPER DEGRAISSANT

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830
Issue date: 08/10/2020 Revision date: 08/10/2020 Supersedes version of: 05/12/2014 Version: 3.0

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product form : Mixture
Product name : 005111 - SUPER DEGRAISSANT
UFI : 9T4F-K0X2-M00F-1G1N
Product code : 005111
Type of product : Aerosol,Cleaner.
Vaporizer : Aerosol

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Main use category : Professional use
Industrial/Professional use spec : Industrial
For professional use only

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

ITW Spraytec
42, rue Gallieni
F-92600 Asnières sur Seine - France
T +33(0)1.40.80.32.32 - F +33(0)1.40.80.32.30
infofds@itwpc.com - www.jelt.fr

1.4. Emergency telephone number

Emergency number : FRANCE :+ 33 (0)1 45 42 59 59

Country	Organisation/Company	Address	Emergency number	Comment
United Kingdom	National Poisons Information Service (Newcastle Centre) Regional Drugs and Therapeutics Centre, Wolfson Unit	Claremont Place Newcastle-upon-Tyne NE1 4LP Newcastle	0344 892 0111	

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Aerosol, Category 1 H222;H229
Skin corrosion/irritation, Category 2 H315
Skin sensitisation, Category 1 H317
Specific target organ toxicity — Single exposure, Category 3, Narcosis H336
Hazardous to the aquatic environment — Chronic Hazard, Category 2 H411
Full text of H statements : see section 16

Adverse physicochemical, human health and environmental effects

No additional information available

005111 - SUPER DEGRAISSANT

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP) :



GHS02

GHS07

GHS09

Signal word (CLP) :

Danger

Contains :

Hydrocarbons, C6, isoalkanes, <5% n-hexane; (R)-p-mentha-1,8-diene; d-limonene

Hazard statements (CLP) :

H222 - Extremely flammable aerosol.
H229 - Pressurised container: May burst if heated.
H315 - Causes skin irritation.
H317 - May cause an allergic skin reaction.
H336 - May cause drowsiness or dizziness.
H411 - Toxic to aquatic life with long lasting effects.
Precautionary statements (CLP) :

P210 - Keep away from heat/sparks/open flames/hot surfaces. — No smoking.
P211 - Do not spray on an open flame or other ignition source.
P251 - Pressurized container: Do not pierce or burn, even after use.
P271 - Use only outdoors or in a well-ventilated area.
P273 - Avoid release to the environment.
P302+P352 - IF ON SKIN: Wash with plenty of soap and water.
P410+P412 - Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.
P501 - Dispose of contents/container to hazardous or special waste collection point, in accordance with local, regional, national and/or international regulation.

2.3. Other hazards

No additional information available

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
Hydrocarbons, C6, isoalkanes, <5% n-hexane	(EC-No.) 931-254-9 (REACH-no) 01-2119484651-34	50 – 70	Flam. Liq. 2, H225 Skin Irrit. 2, H315 STOT SE 3, H336 Asp. Tox. 1, H304 Aquatic Chronic 2, H411
Methylal	(CAS-No.) 109-87-5 (EC-No.) 203-714-2 (REACH-no) 01-2119664781-31	20 – 40	Flam. Liq. 2, H225
Carbon dioxide	(CAS-No.) 124-38-9 (EC-No.) 204-696-9	< 10	Press. Gas (Comp.), H280
(R)-p-mentha-1,8-diene; d-limonene	(CAS-No.) 5989-27-5 (EC-No.) 227-813-5 (EC Index-No.) 601-029-00-7 (REACH-no) 01-2119529223-47	< 5	Flam. Liq. 3, H226 Skin Irrit. 2, H315 Skin Sens. 1, H317 Asp. Tox. 1, H304 Aquatic Acute 1, H400 Aquatic Chronic 1, H410

Product subject to CLP Article 1.1.3.7. The disclosure rules of the components is modified in this case.

Full text of H-statements: see section 16

005111 - SUPER DEGRAISSANT

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures general	: Call a POISON CENTER/doctor/physician if you feel unwell.
First-aid measures after inhalation	: Remove person to fresh air and keep comfortable for breathing.
First-aid measures after skin contact	: Wash skin with plenty of water. Take off contaminated clothing. If skin irritation or rash occurs: Get medical advice/attention.
First-aid measures after eye contact	: Rinse eyes with water as a precaution.
First-aid measures after ingestion	: Call a POISON CENTER/doctor/physician if you feel unwell.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms/effects	: May cause drowsiness or dizziness.
Symptoms/effects after skin contact	: May cause an allergic skin reaction.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media	: Water haze. Carbon dioxide. Foam.
Unsuitable extinguishing media	: Do not use a heavy water stream.

5.2. Special hazards arising from the substance or mixture

Fire hazard	: Extremely flammable aerosol.
Explosion hazard	: Pressurised container: May burst if heated.
Hazardous decomposition products in case of fire	: Thermal decomposition generates : fume. Carbon dioxide. Carbon monoxide.

5.3. Advice for firefighters

Protection during firefighting	: Do not attempt to take action without suitable protective equipment. Self-contained breathing apparatus. Complete protective clothing.
--------------------------------	--

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

6.1.1. For non-emergency personnel

No additional information available

6.1.2. For emergency responders

Protective equipment	: Do not attempt to take action without suitable protective equipment. For further information refer to section 8: "Exposure controls/personal protection".
----------------------	---

6.2. Environmental precautions

Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

For containment	: Collect spillage.
Methods for cleaning up	: Mechanically recover the product.
Other information	: Dispose of materials or solid residues at an authorized site.

6.4. Reference to other sections

For further information refer to section 13.

005111 - SUPER DEGRAISSANT

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

SECTION 7: Handling and storage

7.1. Precautions for safe handling

- Precautions for safe handling : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Do not spray on an open flame or other ignition source. Do not pierce or burn, even after use. Use only outdoors or in a well-ventilated area. Avoid breathing dust/fume/gas/mist/vapours/spray. Avoid contact with skin and eyes. Wear personal protective equipment.
- Hygiene measures : Contaminated work clothing should not be allowed out of the workplace. Wash contaminated clothing before reuse. Do not eat, drink or smoke when using this product. Always wash hands after handling the product.

7.2. Conditions for safe storage, including any incompatibilities

- Storage conditions : Protect from sunlight. Do not expose to temperatures exceeding 50 °C/ 122 °F. Store locked up. Store in a well-ventilated place. Keep container tightly closed. Keep cool.
- Incompatible materials : Sources of ignition. Heat sources. Direct sunlight.
- Storage temperature : < 50 °C

7.3. Specific end use(s)

No additional information available

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

8.1.1 National occupational exposure and biological limit values

Methylal (109-87-5)	
France - Occupational Exposure Limits	
Local name	Méthylal
VME (OEL TWA)	3100 mg/m ³
VME (OEL TWA) [ppm]	1000 ppm
United Kingdom - Occupational Exposure Limits	
Local name	Dimethoxymethane
WEL TWA (OEL TWA) [1]	3160 mg/m ³
WEL TWA (OEL TWA) [2]	1000 ppm
WEL STEL (OEL STEL)	3950 mg/m ³
WEL STEL (OEL STEL) [ppm]	1250 ppm

Carbon dioxide (124-38-9)	
France - Occupational Exposure Limits	
Local name	Carbone (dioxyde de)
VME (OEL TWA)	9000 mg/m ³
VME (OEL TWA) [ppm]	5000 ppm
United Kingdom - Occupational Exposure Limits	
Local name	Carbon dioxide
WEL TWA (OEL TWA) [1]	9150 mg/m ³
WEL TWA (OEL TWA) [2]	5000 ppm
WEL STEL (OEL STEL)	27400 mg/m ³

005111 - SUPER DEGRAISSANT

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Carbon dioxide (124-38-9)

WEL STEL (OEL STEL) [ppm]	15000 ppm
---------------------------	-----------

8.1.2. Recommended monitoring procedures

No additional information available

8.1.3. Air contaminants formed

No additional information available

8.1.4. DNEL and PNEC

No additional information available

8.1.5. Control banding

No additional information available

8.2. Exposure controls

8.2.1. Appropriate engineering controls

Appropriate engineering controls:

Ensure good ventilation of the work station.

8.2.2. Personal protection equipment

8.2.2.1. Eye and face protection

Eye protection:

Chemical goggles or safety glasses

8.2.2.2. Skin protection

Skin and body protection:

Wear suitable protective clothing

Hand protection:

Wear gloves. Nitrile rubber gloves. The choice of appropriate gloves depends not only on the material, but also on other quality criteria that may vary from one manufacturer to another. As the product is a preparation made from several substances, glove material resistance may not be calculated in advance and must be tested before use. The exact penetration time of glove material is to be determined by the manufacturer of protective gloves and respected.

Other skin protection

Materials for protective clothing:

Wear suitable protective clothing

8.2.2.3. Respiratory protection

Respiratory protection:

In case of insufficient ventilation, wear suitable respiratory equipment

8.2.2.4. Thermal hazards

No additional information available

8.2.3. Environmental exposure controls

Environmental exposure controls:

Avoid release to the environment.

005111 - SUPER DEGRAISSANT

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Colour	: Colourless.
Odour	: Organic solvent.
Odour threshold	: No data available
pH	: No data available
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: No data available
Freezing point	: No data available
Boiling point	: No data available
Flash point	: No data available
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Flammability (solid, gas)	: Extremely flammable aerosol.
Vapour pressure	: No data available
Relative vapour density at 20 °C	: No data available
Relative density	: No data available
Density	: 0,65 g/cm ³
Solubility	: insoluble in water. soluble in most organic solvents.
Partition coefficient n-octanol/water (Log Pow)	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available
Explosive properties	: Pressurised container: May burst if heated.
Oxidising properties	: No data available
Explosive limits	: No data available

9.2. Other information

No additional information available

SECTION 10: Stability and reactivity

10.1. Reactivity

Extremely flammable aerosol. Pressurised container: May burst if heated.

10.2. Chemical stability

Stable under normal conditions. Extremely flammable aerosol. Heating may cause a fire or explosion.

10.3. Possibility of hazardous reactions

None under normal conditions.

10.4. Conditions to avoid

Avoid contact with hot surfaces. Heat. No flames, no sparks. Eliminate all sources of ignition.

10.5. Incompatible materials

Strong acids. Strong bases.

10.6. Hazardous decomposition products

Thermal decomposition generates : fume. Carbon dioxide. Carbon monoxide.

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute toxicity (oral)	: Not classified
Acute toxicity (dermal)	: Not classified

005111 - SUPER DEGRAISSANT

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Acute toxicity (inhalation) : Not classified

Hydrocarbons, C6, isoalkanes, <5% n-hexane

LD50 oral rat	> 36750 mg/kg
LD50 dermal rabbit	> 3350 ml/kg
LC50 Inhalation - Rat	259354 mg/l/4h

Methylal (109-87-5)

LD50 oral rat	100 mg/kg
LD50 dermal rabbit	300 mg/kg
LC50 Inhalation - Rat	0,5 mg/l

Skin corrosion/irritation : Causes skin irritation.
Serious eye damage/irritation : Not classified
Respiratory or skin sensitisation : May cause an allergic skin reaction.
Germ cell mutagenicity : Not classified
Carcinogenicity : Not classified

Reproductive toxicity : Not classified

STOT-single exposure : May cause drowsiness or dizziness.

Hydrocarbons, C6, isoalkanes, <5% n-hexane

STOT-single exposure	May cause drowsiness or dizziness.
----------------------	------------------------------------

STOT-repeated exposure : Not classified

Aspiration hazard : Not classified

005111 - SUPER DEGRAISSANT

Vaporizer	Aerosol
-----------	---------

SECTION 12: Ecological information

12.1. Toxicity

Ecology - general : Toxic to aquatic life with long lasting effects.
Hazardous to the aquatic environment, short-term (acute) : Not classified
Hazardous to the aquatic environment, long-term (chronic) : Toxic to aquatic life with long lasting effects.

Hydrocarbons, C6, isoalkanes, <5% n-hexane

LC50 - Fish [1]	> 1 mg/l
EC50 - Crustacea [1]	3,87 mg/l
ErC50 algae	30 mg/l

Methylal (109-87-5)

LC50 - Fish [1]	> 1000 mg/l
EC50 - Crustacea [1]	> 1200 mg/l

005111 - SUPER DEGRAISSANT

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

12.2. Persistence and degradability

No additional information available

12.3. Bioaccumulative potential

Hydrocarbons, C6, isoalkanes, <5% n-hexane

Partition coefficient n-octanol/water (Log Kow)	4
---	---

Carbon dioxide (124-38-9)

Partition coefficient n-octanol/water (Log Pow)	0,83
---	------

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

No additional information available

12.6. Other adverse effects

No additional information available

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product/Packaging disposal recommendations : Dispose in a safe manner in accordance with local/national regulations. Container under pressure. Do not drill or burn even after use.

SECTION 14: Transport information

In accordance with ADR / IMDG / IATA / ADN / RID /

ADR	IMDG	IATA	ADN	RID
14.1. UN number				
UN 1950	UN 1950	UN 1950	UN 1950	UN 1950
14.2. UN proper shipping name				
AEROSOLS	AEROSOLS	Aerosols, flammable	AEROSOLS	AEROSOLS
Transport document description				
UN 1950 AEROSOLS, 2.1, (D), ENVIRONMENTALLY HAZARDOUS	UN 1950 AEROSOLS, 2.1, MARINE POLLUTANT/ENVIRONMENTALLY HAZARDOUS	UN 1950 Aerosols, flammable, 2.1, ENVIRONMENTALLY HAZARDOUS	UN 1950 AEROSOLS, 2.1, ENVIRONMENTALLY HAZARDOUS	UN 1950 AEROSOLS, 2.1, ENVIRONMENTALLY HAZARDOUS
14.3. Transport hazard class(es)				
2.1	2.1	2.1	2.1	2.1
14.4. Packing group				
Not applicable	Not applicable	Not applicable	Not applicable	Not applicable

005111 - SUPER DEGRAISSANT

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

14.5. Environmental hazards

Dangerous for the environment : Yes	Dangerous for the environment : Yes Marine pollutant : Yes	Dangerous for the environment : Yes	Dangerous for the environment : Yes	Dangerous for the environment : Yes

No supplementary information available

14.6. Special precautions for user

Overland transport

Classification code (ADR)	: 5F
Special provisions (ADR)	: 190, 327, 344, 625
Limited quantities (ADR)	: 1I
Excepted quantities (ADR)	: E0
Packing instructions (ADR)	: P207, LP02
Special packing provisions (ADR)	: PP87, RR6, L2
Mixed packing provisions (ADR)	: MP9
Transport category (ADR)	: 2
Special provisions for carriage - Packages (ADR)	: V14
Special provisions for carriage - Loading, unloading and handling (ADR)	: CV9, CV12
Special provisions for carriage - Operation (ADR)	: S2
Tunnel restriction code (ADR)	: D

Transport by sea

Special provisions (IMDG)	: 63, 190, 277, 327, 344, 959
Limited quantities (IMDG)	: SP277
Excepted quantities (IMDG)	: E0
Packing instructions (IMDG)	: P207, LP02
Special packing provisions (IMDG)	: PP87, L2
EmS-No. (Fire)	: F-D
EmS-No. (Spillage)	: S-U
Stowage category (IMDG)	: None

Air transport

PCA Excepted quantities (IATA)	: E0
PCA Limited quantities (IATA)	: Y203
PCA limited quantity max net quantity (IATA)	: 30kgG
PCA packing instructions (IATA)	: 203
PCA max net quantity (IATA)	: 75kg
CAO packing instructions (IATA)	: 203
CAO max net quantity (IATA)	: 150kg
Special provisions (IATA)	: A145, A167
ERG code (IATA)	: 10L

Inland waterway transport

Classification code (ADN)	: 5F
Special provisions (ADN)	: 19, 327, 344, 625
Limited quantities (ADN)	: 1 L
Excepted quantities (ADN)	: E0
Equipment required (ADN)	: PP, EX, A
Ventilation (ADN)	: VE01, VE04
Number of blue cones/lights (ADN)	: 1

Rail transport

Classification code (RID)	: 5F
Special provisions (RID)	: 190, 327, 344, 625
Limited quantities (RID)	: 1L
Excepted quantities (RID)	: E0
Packing instructions (RID)	: P207, LP02
Special packing provisions (RID)	: PP87, RR6, L2
Mixed packing provisions (RID)	: MP9
Transport category (RID)	: 2
Special provisions for carriage – Packages (RID)	: W14
Special provisions for carriage - Loading, unloading and handling (RID)	: CW9, CW12

005111 - SUPER DEGRAISSANT

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Colis express (express parcels) (RID) : CE2
Hazard identification number (RID) : 23

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

Contains no substance subject to Regulation (EU) No 649/2012 of the European Parliament and of the Council of 4 July 2012 concerning the export and import of hazardous chemicals.

Contains no substance subject to Regulation (EU) No 2019/1021 of the European Parliament and of the Council of 20 June 2019 on persistent organic pollutants

15.1.2. National regulations

France

Occupational diseases

Code	Description
RG 66	Occupational rhinitis and asthma
RG 84	Conditions caused by liquid organic solvents for professional use: saturated or unsaturated aliphatic or cyclic liquid hydrocarbons and mixtures thereof; liquid halogenated hydrocarbons; nitrated derivatives of aliphatic hydrocarbons; alcohols; glycols, glycol ethers; ketones; aldehydes; aliphatic and cyclic ethers, including tetrahydrofuran; esters; dimethylformamide and dimethylacetamine; acetonitrile and propionitrile; pyridine; dimethylsulfone and dimethylsulfoxide

Germany

Water hazard class (WGK) : WGK 2, Significantly hazardous to water (Classification according to AwSV, Annex 1)

Hazardous Incident Ordinance (12. BImSchV) : Is not subject of the Hazardous Incident Ordinance (12. BImSchV)

Netherlands

SZW-lijst van kankerverwekkende stoffen : None of the components are listed

SZW-lijst van mutagene stoffen : None of the components are listed

NIET-limitatieve lijst van voor de voortplanting giftige stoffen – Borstvoeding : None of the components are listed

NIET-limitatieve lijst van voor de voortplanting giftige stoffen – Vruchtbaarheid : None of the components are listed

NIET-limitatieve lijst van voor de voortplanting giftige stoffen – Ontwikkeling : None of the components are listed

NIET-limitatieve lijst van voor de voortplanting giftige stoffen – Ontwikkeling : None of the components are listed

NIET-limitatieve lijst van voor de voortplanting giftige stoffen – Ontwikkeling : None of the components are listed

NIET-limitatieve lijst van voor de voortplanting giftige stoffen – Ontwikkeling : None of the components are listed

Denmark

Danish National Regulations : Young people below the age of 18 years are not allowed to use the product

15.2. Chemical safety assessment

No additional information available

SECTION 16: Other information

Full text of H- and EUH-statements:

Aquatic Acute 1	Hazardous to the aquatic environment — Acute Hazard, Category 1
Aquatic Chronic 1	Hazardous to the aquatic environment — Chronic Hazard, Category 1
Aquatic Chronic 2	Hazardous to the aquatic environment — Chronic Hazard, Category 2
Asp. Tox. 1	Aspiration hazard, Category 1
Flam. Liq. 2	Flammable liquids, Category 2

005111 - SUPER DEGRAISSANT

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Flam. Liq. 3	Flammable liquids, Category 3
Press. Gas (Comp.)	Gases under pressure : Compressed gas
Skin Irrit. 2	Skin corrosion/irritation, Category 2
Skin Sens. 1	Skin sensitisation, Category 1
STOT SE 3	Specific target organ toxicity — Single exposure, Category 3, Narcosis
H222	Extremely flammable aerosol.
H225	Highly flammable liquid and vapour.
H226	Flammable liquid and vapour.
H229	Pressurised container: May burst if heated.
H280	Contains gas under pressure; may explode if heated.
H304	May be fatal if swallowed and enters airways.
H315	Causes skin irritation.
H317	May cause an allergic skin reaction.
H336	May cause drowsiness or dizziness.
H400	Very toxic to aquatic life.
H410	Very toxic to aquatic life with long lasting effects.
H411	Toxic to aquatic life with long lasting effects.

Safety Data Sheet (SDS), EU

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.