



ITEM. 06888

# SIP SUB 3075 DIRTY WATER PUMP

POWERFUL DIRTY WATER PUMP FOR DOMESTIC & LIGHT COMMERCIAL USE



COMES WITH  
A 2-YEAR  
STANDARD  
WARRANTY\*

FIND OUT MORE AT  
[SIP-GROUP.COM/WARRANTY](http://SIP-GROUP.COM/WARRANTY)



## PRODUCT OVERVIEW

The **SIP SUB 3075 Dirty Water Pump** is ideal for draining dirty water from a flooded cellar, basement, small water or collection tank, well or pond. This pump has been designed for intermittent use.

Water pumps can help prevent costly damage to property or work areas from recurring rainwater or groundwater. This pump can also be used for a variety of garden maintenance purposes.

## FEATURES & BENEFITS

- ✓ **POWERFUL BRUSHLESS INDUCTION MOTOR (750w/1hp)**  
Draws water at a max. flow rate of 14,100ltr/hr through an impeller at the pump base. The heavy-duty wound motor is durable and lightweight.
- ✓ **FITTED FLOAT SWITCH**  
Ensures the pump functions unaided when the activation depth (400mm) is reached. This prevents the pump from running dry and overheating when in use.
- ✓ **MAX. 8MTR PUMPING HEAD**  
Discharges water flow to a max. height of 8mtr through hose or pipe connected to pump outlet. This ensures the intended area or item is drained quickly.
- ✓ **PARTICLE CAPACITY**  
Suitable for draining dirty water with particles to max. diameter of 35mm.
- ✓ **LIGHTWEIGHT, COMPACT DESIGN**  
Includes a carry handle for portability and lowering into water (7mtr max. operating depth). A mounted power cable hook provides added safety.

For over 50 years, SIP Industrial Products Limited has been a flagship supplier of high-quality equipment and machinery to the ever-growing engineering, construction, automotive, and agricultural marketplaces.



ITEM. 06888

# SIP SUB 3075 DIRTY WATER PUMP

## OTHER FEATURES

### HIGH-GRADE CARBON STEEL PUMP SHAFT

High-tensile strength compound for long life use.

### POWER CABLE

Fitted with a 10mtr length cable for greater versatility.

## APPLICATIONS & USES

Quickly drains flooded areas.

Effective for a variety of garden maintenance purposes.

Suitable for domestic or light commercial use.

Intended for intermittent use.

## TECHNICAL INFORMATION

ITEM NO.	06888
Input Supply	230v 50Hz
Motor Power	750w (1hp)
Flow Rate	14,100ltr/hr
Outlet	25mm Ø - 40mm Ø 1" BSP
Max. Pumping Head	8mtr
Max. Operating Depth	7mtr
Max. Particle Diameter	Ø 35mm
Max. Water Temperature	35°C
Body Type	Plastic
Pump Type	Dirty Water
Cable Length	10mtr
Protection	IPX8
Net Weight	4.80kg
Gross Weight	5.30kg
Product Dimensions	340(H) x 250(W) x 180mm(D)
Packaged Dimensions	420(H) x 350(W) x 370mm(D)