

# CBC-PRC 3-FC-FS6 8-21 HR 800V - Coupler connector



1441143

<https://www.phoenixcontact.com/gb/products/1441143>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Coupler connector, Range of articles: ArcZero, color: black, number of positions: 3, min. conductor cross section: 1.5 mm<sup>2</sup>, max. conductor cross section: 6 mm<sup>2</sup>, rated voltage: 800 VDC, rated current: 20 A, Connection method: Screw connection, Contact connection type: Socket, min. cable diameter: 8 mm, max. cable diameter: 21 mm, Maximum load when disconnecting: 16 kW, scope: DC-Grids

## Your advantages

- Safe connection and disconnection under load
- Fast disconnection of flying leads
- Time-saving maintenance or replacement of connected devices
- Robust outdoor design even for extreme conditions
- Particularly durable and economical

## Commercial data

Item number	1441143
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	ABLFBA
Product key	ABLFBA
GTIN	4063151821975
Weight per piece (including packing)	157.284 g
Weight per piece (excluding packing)	157.284 g
Customs tariff number	85366990
Country of origin	DE



# CBC-PRC 3-FC-FS6 8-21 HR 800V - Coupler connector



1441143

<https://www.phoenixcontact.com/gb/products/1441143>

## Technical data

### Notes

Note on application	Maximum load when disconnecting: 16 kW (6.7 $\mu$ F/5 mH)
Note on application	Maximum load when connecting: 2 kW (6.7 $\mu$ F/5 mH)
Note on application	Observe the specifications of the packing slip.
Notes on safety	Fit the protective cap when not plugged in.
Order information:	The release lever for manual release can be found in the accessories section.

### Product properties

Product type	Installation connector
Product family	ArcZero
Area of application	DC-Grids
Number of positions	3

### Insulation characteristics

Protection class	II (plastic housing)
------------------	----------------------

### Electrical properties

Nominal voltage ATD	800 VDC (III/2.00) in accordance with IEC 61984
	250 VDC Minimum system voltage
	500 VDC (III/2.00) in accordance with IEC 61535
	600 VDC (III/2.00) in accordance with UL 2238 / UL 2237
Rated current	20 A (With 2.5 mm <sup>2</sup> conductor cross section in accordance with IEC 61984)

### Dimensions

Width	37.6 mm
Height	39 mm
Length	159 mm

### Material specifications

Color (Housing)	black (RAL 9005)
Material Housing	PPE

### Cable/line

External cable diameter	8 mm ... 21 mm
Single wire, cross section	1.5 mm <sup>2</sup> 6 mm <sup>2</sup>
Stripping length of the individual wire	13 mm (Lay PE conductor 10 mm leading)
Halogen-free	yes (in accordance with IEC 61249-2-21:2003- 11 Cl.3.1)

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	500 (under rated load)
-----------------------------	------------------------



# CBC-PRC 3-FC-FS6 8-21 HR 800V - Coupler connector



1441143  
<https://www.phoenixcontact.com/gb/products/1441143>

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP66
	IP68 (2 m / 2 h)
	IP69
Ambient temperature (operation)	-40 °C ... 105 °C (observe derating)
Ambient temperature (storage/transport)	-40 °C ... 105 °C
Ambient temperature (assembly)	-20 °C ... 60 °C

## Standards and regulations

Standards/specifications	IEC 61984
	IEC TS 62735-1



# CBC-PRC 3-FC-FS6 8-21 HR 800V - Coupler connector




1441143

<https://www.phoenixcontact.com/gb/products/1441143>

## Drawings

Diagram



Derating




# CBC-PRC 3-FC-FS6 8-21 HR 800V - Coupler connector



1441143  
<https://www.phoenixcontact.com/gb/products/1441143>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1441143>

	<b>VDE approval of drawings</b>			
	Approval ID: 304284-TL3-1			
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	80 V	20 A	-	1.5 - 6



# CBC-PRC 3-FC-FS6 8-21 HR 800V - Coupler connector



1441143  
<https://www.phoenixcontact.com/gb/products/1441143>

## Classifications

### ECLASS

ECLASS-13.0	27440605
-------------	----------

### ETIM

ETIM 9.0	EC002560
----------	----------



# CBC-PRC 3-FC-FS6 8-21 HR 800V - Coupler connector



1441143

<https://www.phoenixcontact.com/gb/products/1441143>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
	Triphenyl phosphate(CAS: 115-86-6)
SCIP	a506d761-ba8f-4434-9e18-5fc48e3f55a6

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)