

## Features

- Excellent molten splash and flame resistance
- Continuous working temperature of 200°C (500°F)
- Superb abrasion and moisture resistance
- Very flexible and available in different colours
- Provides protection from ozone and UV
- Insulates against energy loss in piping and hosing
- Max short time exposure 1650°C (3000°F)
- Available in Red, Black, Yellow, Blue, White and SILVER

## RS PRO Fire Sleeve SILVER 1M

RS Stock No.: 0731333



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

RS Pro Fire Sleeve is designed to protect hoses, wires and cables from the hazards of high heat and occasional flame. Made of braided fiberglass yarns in a flexible substrate, it is then coated with high grade silicone rubber. The thick formulation of silicone rubber sheds molten splash, slag, welding splatter, electrical or grinding sparks and contamination. RS Pro Fire Sleeve's key applications are protecting hydraulic hoses, cables and wiring. Used in metallurgy, steel mills, glass works, marine industry and petrochemical industry.

## General Specifications

Part Number	Ordering Size (mm)
0731312	4
0730404	6
0730405	8
0730406	10
0730407	12
0731313	14
0731314	16
0731315	19
0731317	22
0731318	25
0731319	28
0731320	32
0731321	35
0731323	38
0731324	41
0731325	51
0731326	57
0731327	63
0731328	70
0731329	76
0731330	83
0731331	89
0731332	95
0731333	102
0733735	114
0733736	127
0733737	140
0733740	168
0733741	180
0733742	203

## Approvals

Declarations	Compiles with EN 45545-2 Tested to ISO 11925-2
Standards Met	Meets requirement for IEC 60695-11-10 Classified as HB an V0 Meets requirements for UL94 V0,V1,V2