

12 V Optical Smoke Detector

Art. no. RM1000

Page 1 of 1



- Suitable for connecting to alarm and fire detection systems
- Detects visible smoke particles
- Self-adjusting
- Potential-free alarm relay
- Tested according to EN54-7

The 12 V optical smoke detector reacts to visible smoke particles. If too much smoke enters its measuring chamber, an alarm is triggered. In the measuring chamber, an integrated infrared light source generates a light pulse every 8 seconds. Smoke particles from a fire change the light signal received by the light diode. A relay trips and the alarm center reports a fire alarm. The 12 V optical smoke detector is mounted on the ceiling in the center of the room. The minimum distance to the side wall should be 30cm. We recommend a separate smoke detector for each entrance area, staircase, living-room, and bedroom. By changing a jumper, you can configure the optical smoke detector as NO or as NC detector. It is therefore suitable for every wired alarm system. The smoke detector is supplied externally with 12V operating voltage and is EN54 certified.

Technical Data:

Dimensions	(HxD) 46x100 mm
Connections	Screw terminal NO or NC, 1A at 30V DC
Width	100 mm
Type of detection	Optical
Housing material	ABS
Height	46 mm
Power consumption	0,368
Max. operating temperature	50 °C
Max. humidity	95 %

Installation location	Ceiling
Net weight	0.13 kg
Sensor type	Photodiode
DC voltage supply	10,5-13,8 V
Status display	Yes
Power consumption	35 mA
Certifications	EN54-7