

# LS-EMP-AL (49X15) BK - Device marker



0831671

<https://www.phoenixcontact.com/gb/products/0831671>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Device marker, Aluminum label, black, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, mounting type: latching, Number of individual labels: 24, text field height: 15 mm, text field width: 49 mm



## Your advantages

- Aluminum equipment marking for snapping into marker carriers
- Identification made from metal, high strength in a lightweight design
- Increased durability due to the decoratively anodized surface

## Commercial data

Item number	0831671
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	BG241D
Product key	BG241D
Catalog page	Page 289 (C-3-2019)
GTIN	4046356926058
Weight per piece (including packing)	80.16 g
Weight per piece (excluding packing)	80.16 g
Customs tariff number	76169990
Country of origin	CN

## Technical data

### Product properties

Product type	Device marking
Type	Laser sheet

### Marking

Number of individual labels	24
Identification technology	Direct laser marking

### Mounting

Mounting type	latching
---------------	----------

### Material specifications

RoHS compliant	yes
Color	black (RAL 9005)
Material	Aluminum
Components	free from silicone, halogen, and cadmium

### Environmental and real-life conditions

#### Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

#### Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

#### Tesafilm test

Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed

#### UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

#### Weathering-resistance

Specification	ISO 4892-2:2013-03
Result	Test passed
Test duration	1500 h
Procedure	A

#### Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 150 °C (180 °C)	Test passed

## Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Acetone (99 %) [CAS No. 67-64-1]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Acetone (99 %) [CAS No. 67-64-1]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed

## Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

## Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

## Salt spray test

Specification	ISO 9227:2012-05
Result	Test passed
Test duration	336 h

## High pressure test

Specification	ISO 20653:2013-02
Result	Test passed

## Ambient conditions

Ambient temperature (operation)	-25 °C ... 70 °C (At temperatures above 80 °C there might be a slight change to the material surface)
---------------------------------	---

# LS-EMP-AL (49X15) BK - Device marker



0831671

<https://www.phoenixcontact.com/gb/products/0831671>

Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

## Dimensions

Width	48.7 mm
Length	14.8 mm
Material strength	0.80 mm

## Text field

Text field width	49 mm
Text field height	15 mm

## Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

0831671

<https://www.phoenixcontact.com/gb/products/0831671>

## Classifications

### ECLASS

ECLASS-11.0	27281106
ECLASS-12.0	27281106
ECLASS-13.0	27281106

### ETIM

ETIM 9.0	EC001288
----------	----------

### UNSPSC

UNSPSC 21.0	39131700
-------------	----------

# LS-EMP-AL (49X15) BK - Device marker



0831671

<https://www.phoenixcontact.com/gb/products/0831671>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)