

Product datasheet

Specifications



PILOT LIGHT 28V 30MM SK +OPTIONS

Local distributor code:

387212566

9001SKP35LGG9

EAN Code: 3389118037540

Main

| | |
|---------------------------|-------------------|
| Range of product | Harmony 9001SK |
| Product or component type | Pilot light |
| Device short name | 9001SK |
| Lens type | Domed plastic |
| Light block supply | Direct 24 V AC/DC |

Complementary

| | |
|---|---|
| Bezel material | Plastic |
| Mounting diameter | 30 mm |
| Shape of signaling unit head | Round |
| Cap/operator or lens colour | Green |
| Light source | LED |
| Bulb base | BA 9s |
| [Us] rated supply voltage | 24...28 V AC/DC |
| Tightening torque | 0.8 N.m conforming to IEC 60947-1 |
| Shape of screw head | Cross slotted |
| Connections - terminals | Screw clamp terminals, 1 x 0.22...2 x 1.5 mm ² conforming to IEC 60947-1 |
| [Ith] conventional free air thermal current | 10 A |
| Short-circuit protection | 10 A cartridge fuse conforming to IEC 60947-5-1 |
| [Ui] rated insulation voltage | 250 V (pollution degree 2) conforming to IEC 60947-1 |
| [Uimp] rated impulse withstand voltage | 2.5 kV conforming to IEC 60947-1 |
| Operating position | Any position |
| CAD overall width | 54 mm |
| CAD overall height | 70 mm |
| CAD overall depth | 42 mm |
| Net weight | 0.082 kg |
| Device presentation | Complete product |
| Lens type | Domed |
| [Us] rated supply voltage | 24...28 V |
| Light source colour | Green |
| Lens material | Polycarbonate |

| | |
|--------------|-------|
| Size | 30 mm |
| Light source | LED |

Environment

| | |
|---------------------------------------|---|
| Electrical shock protection class | Class II conforming to IEC 61140 |
| Protective treatment | TC |
| IP degree of protection | IP65 IP66 |
| NEMA degree of protection | NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4 NEMA 4X |
| Vibration resistance | 7 gn (f= 2...500 Hz) conforming to IEC 60068-2-6 |
| Shock resistance | 50 gn conforming to IEC 60068-2-27 |
| Ambient air temperature for operation | -25...70 °C |
| Ambient air temperature for storage | -40...70 °C |
| Standards | UL 508 IEC 60947-5-4 CSA C22.2 No 14 JIS C 852 JIS C8201-5-1 IEC 60947-5-1 IEC 60947-1 JIS C8201-1 |
| Product certifications | NEMA UL 508 |

Packing Units

| | |
|------------------------------|------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 4.500 cm |
| Package 1 Width | 5.500 cm |
| Package 1 Length | 9.000 cm |
| Package 1 Weight | 85.000 g |
| Unit Type of Package 2 | S01 |
| Number of Units in Package 2 | 16 |
| Package 2 Height | 15.000 cm |
| Package 2 Width | 15.000 cm |
| Package 2 Length | 40.000 cm |
| Package 2 Weight | 1.504 kg |
| Unit Type of Package 3 | P12 |
| Number of Units in Package 3 | 512 |
| Package 3 Height | 45.000 cm |
| Package 3 Width | 80.000 cm |
| Package 3 Length | 120.000 cm |

Package 3 Weight 60.128 kg

Logistical informations

Country of origin FR

Contractual warranty

Warranty (in months) 18



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

[Environmental Disclosure](#)

[Product Environmental Profile](#)

Use Better



Materials and Substances

Packaging made with recycled cardboard

Yes

Packaging without single use plastic

Yes

[EU RoHS Directive](#)

Pro-active compliance (Product out of EU RoHS legal scope)

REACH Regulation

[REACH Declaration](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

End of life manual availability

[End of Life Information](#)

Take-back

No


WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Dimensions Drawings

Dimensions



e panel thickness: 1 to 6 mm / 0.04 to 0.24 in.

Image of product / Alternate images

Alternative



