

Technical data sheet

Article number:
554-51701

TLFX254YE



Product Group	Shrinkable markers "Continuous Tube", thermal transfer
Product Family	TLFX – 2:1 Rail Limited Fire Hazard
Material	Polyolefin, cross-linked (PO-X)
Colour	Yellow (YE)
Elongation at break (min.) [Test method]	4.5 % [ASTM D2671]
Heat Aging Test [Test method]	168h/150°C [ASTM D638]
Heat Shock Test	4h/150°C
Longitudinal Change After Shrinkage [Test method]	-6% [UL 224]
Low Temperature Test [Test method]	1h/-30°C [ASTM D2671]
Min. Shrink Temperature - °C	+70 °C
Operating Temperature	-55 °C to +125 °C
Oxygen index [Test method]	33.4 % [ISO 4589]
Package Content	30 m
Package Content packed in	carton
Print Method	thermal transfer print
Recommended Ribbon Type	TTDTHOUT
Recov. Ø d max.	12.7 mm
Shrink Ratio	2:1
Specifications	EN 45545-2
Supplied Ø D min.	25.4 mm
Tensile Strength [Test method]	12 MPa [ASTM D2671]
Thermal Transfer Printer	TT431, TT4030DS, TT4030
Toxicity index [Test method]	0.02 CITg [ISO 5659-2]
Volume Resistance [Test method]	10 ¹⁴ Ω cm [ASTM D257]
Wall (WT)	0.69 mm

HF ✓ LFH ✓ RoHS ✓

EN 45545-2