

Chain Saw LXT®

DUC307

18V • 30 cm / 12" • 7,7 m/s • 3/8"

Cordless Chain Saw LXT® with excellent work efficiency.

Higher lock torque achieved by adding gear reduction mechanism and intended for use by residential carpenters and DIY users. The rear handle structure and design is easy to use and very ergonomic to use.



Technical specifications

Voltage LXT	✓
Nominal Battery Voltage	18 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Max. Chain Speed (No Load)	7,7 m/s
Chain Pitch	3/8 "
Chain Gauge	0,043 "
Chain Gauge	1,1 mm
Number of Drive Links	46
Chain Oil Tank	150 ml
Brushless Motor	✓
chain bar length	300 mm (12")
Vibration Level, Cutting Wood	4,9 m/s ²
Vibration Uncertainty (K Factor), Cutting Wood	1,5 m/s ²
Sound Power Level (L _{WA})	97 dB(A)
Sound Pressure Level (L _{pA})	86 dB(A)

User benefits

- Brushless maintenance-free and long-life motor
- Battery protection circuit protects against overloading, over-discharging and over-heating
- Low noise level for pleasant work.

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing