




Connectors > Automotive Connectors > Automotive Connector Accessories > Other Automotive Connector Accessories



Primary Product Color: **Black**
Primary Product Material: **PBT**
Automotive Connector Accessory Type: **Mounting Clip**
Operating Temperature Range: **-40 – 140 °C [-40 – 284 °F]**

Features

Product Type Features

Automotive Connector Accessory Type	Mounting Clip
-------------------------------------	---------------

Body Features

Primary Product Color	Black
Primary Product Material	PBT

Usage Conditions

Operating Temperature Range	-40 – 140 °C[-40 – 284 °F]
-----------------------------	----------------------------

Industry Standards

Compatible With Agency/Standards Products	JIS
UL Flammability Rating	UL 94HB

Packaging Features

Packaging Method	Bag
Packaging Quantity	100

Other

Serviceable	Yes
-------------	-----



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-T319-CH8172
TH/025 CONNECTOR SYSTEM,
HOUSING



TE Part # 1981831-1
WIRECOVER 126P TYPE VI 0.64/2.3II
SEALED

Also in the Series | 0.64/025 Connector System



Automotive Connector Caps & Covers (5)	Automotive Connector Locks & Position Assurance(1)	Automotive Housings(120)	Automotive Terminals(17)
Connector Seals & Cavity Plugs(1)	Other Automotive Connector Accessories(4)	PCB Headers & Receptacles(149)	Rectangular Power Connectors(6)

Customers Also Bought

TE Part #CAT-T319-CH8172 TH/.025 CONNECTOR SYSTEM, HOUSING	TE Part #1939932-1 0.50/1.0 SEALED LEVER 140POS	TE Part #179631-1 DIAGNOSTIC PLUG HSG 16P NARU.	TE Part #2-5353016-2 040 III HD 105POS CAP ASSY H RND
TE Part #1612435-1 025/040 SER 167P STD CAP HSG A	TE Part #1565061-1 SOLIS SPLICED P-38	TE Part #8-5175446-1 HYBRID I/O CAP ASSY 42P	TE Part #5-5353468-1 HIBRID I/O CAP HSG ASSY 76P

Documents

Product Drawings
0.64/2.3II SEALED CLIP

Japanese

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1939393-1_D.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_1939393-1_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1939393-1_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

Japanese

Product Specification

Japanese

Instruction Sheets

Instruction Sheet (non U.S.)

English

Instruction Sheet (non U.S.)

Japanese