



Switches > Toggle Switches



Contact Current Rating: **.4 A**
Configuration (Pole-Throw): **Single Pole - Double Throw**
Operating Function: **On Off On**
Number of Positions: **3**
Operating Voltage: **20 VDC**

Features

Product Type Features

Sealed Device	Yes
Switch Connection Type	Printed Circuit
Toggle Style	Baton Short
Switch Type	Toggle Switch

Configuration Features

Configuration (Pole-Throw)	Single Pole - Double Throw
Operating Function	On Off On
Number of Positions	3

Electrical Characteristics

Contact Resistance	10 mΩ
Insulation Resistance	1000 MΩ
Dielectric Withstanding Voltage (Max)	1000 VAC
Contact Current Rating	.4 A
Operating Voltage	20 VDC

Body Features

Case Color	Black
Product Orientation	Vertical
Bushing Style	Unthreaded



Contact Features

Contact Base Material	Copper Alloy
Switch Contact Plating Material	Gold

Housing Features

Process Sealed	No
----------------	----

Dimensions

Toggle Length	5.61 mm[.221 in]
---------------	------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (3.7% in 74019106) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling



based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 1825219-2
[TT11AGPC104](#)




TE Part # 1825222-3
[TT13D2T04](#)




TE Part # 1825219-4
[TT11DGRA104](#)


Customers Also Bought




TE Part #374182-E
[STVM 6-10 M ABC VVV 4-00 0606 * * 137 E0](#)




TE Part #87224-5
[05 MODII HDR SRST UNSHRD .100](#)




TE Part #4-1879745-6
[RP 1J 1K62 0.1% 15PPM CUT LENGTH](#)




TE Part #2-1879745-7
[RP 1J 1K02 0.1% 15PPM CUT LENGTH](#)




TE Part #CONMCX001-SMD-T
[MCX Jack 50 Ohm PCB Surface Mount](#)




TE Part #1879745-7
[RP 1J 634R 0.1% 15PPM CUT LENGTH](#)




TE Part #3-1879745-6
[RP 1J 1K27 0.1% 15PPM CUT LENGTH](#)



TE Part #6-1618400-7
[EV200ARANA=CONTACTOR SPST-NO, 28Vdc Coil](#)



TE Part #ADP-SMAF-SMAF-B-G
[SMA Jack to SMA Jack Bulkhead](#)



TE Part #7-1879745-3
[RP 1J 3K09 0.1% 15PPM CUT LENGTH](#)

Documents

- CAD Files
- 3D PDF
- 3D
- Customer View Model



[ENG_CVM_CVM_1825219-6_O.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1825219-6_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1825219-6_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SWITCHES_CORE_PROGRAM_CATALOG](#)

English

[2-1773458-4_TINY_TOGGLE_SERIES_SWITCHES](#)

English