



Entra-Plush

Crush-resistant carpet doormat

- Effective carpet doormat for floor protection.
- Crush resistant, quick drying carpet surface.
- Ideal for wiping moisture from wet footwear.
- Polypropylene fibres scrape and trap dirt.
- Slip and stain-resistant PVC 'stay in place' backing.

Overall product height: 7mm (pile height: 4mm)
Total weight: 2.7kg/m²



Red



Grey



Blue



Green



Brown

Dimensions (m.)	Weight Kg	Packaging Dimensions (cm.)	Packaging Type	Packaging Volume (m.)	Packaging Quantity	Colour	Part Code
0.6 x 0.9	2	17.5 x 17.5 x 75	Box	0.02	1	Grey	PP060001
						Brown	PP050001
						Blue	PP020001
						Green	PP040001
						Red	PP030001
0.9 x 1.5	5	17.5 x 17.5 x 105	Box	0.02	1	Grey	PP060002
						Brown	PP050002
						Blue	PP020002
						Green	PP040002
						Red	PP030002
1.2 x 1.8	8	23 x 23 x 124	Box	0.02	1	Grey	PP060003
						Brown	PP050003
						Blue	PP020003
						Green	PP040003
						Red	PP030003

Surface Material:	2950 Denier Continuous Filament solution dyed Polypropylene Yarn
Backing Material:	Specially formulated non staining Vinyl
Operating Temperature:	Ambient
Resistance to Chemicals:	N/A
Environmental Resistance:	Suitable for wet and dry environments. For indoor use only.
Containment:	5.4 litres/square metre
UV Resistance:	Yes

Continued on next page

United Kingdom

COBA Europe Ltd
Marlborough Drive
Fleckney, Leicestershire
LE8 8UR

+44 (0)116 240 1088
sales@cobaurope.com
www.cobaurope.com

Germany

COBA Europe GmbH
Pullenweg 1 - 3
41352 Korschenbroich

+49 (2161) 2945-0
verkauf@cobaurope.de
www.cobaurope.de

Slovakia

COBA Europe s.r.o.
Terchová - Vyšné Kamenec 11
SK-013 06

+421 41 507 11 12
sales@cobaurope.sk
www.cobaurope.sk

The information contained within this datasheet is for guidance only. The data and suggested application are not exhaustive. All dimensions quoted are nominal figures. Please note that some products may be subject to a degree of shrinkage when installed into some applications.

Typical Applications: Lobbies, Hallways, Entry areas and doorways.
 Installation Method: Loose lay.
 Accessories: N/A
 Cleaning Method: Vacuum top surface.

Product Performance:

Fatigue: N/A
 Slip Resistance: ●
 Wear: ● ●
 Low ‡ High: ● → ● ● ● ● ●

Flame Retardancy: DOC-FF-1-70
 Country of Origin: USA

Technical Features: According to:

Manufacturing process	ISO 2424 / BS 5557	Vuilvang
Surface aspect		Cutpile
Pile material		100% PP
Primary backing	ISO 2424 / BS 5557	Collback TM80
Machine guage	DIN 61151 / BS 5557	1/8" C
Backing	ISO 2424	PVC
Pile height	ISO 1766 / BS 4223 Clause 10	4.0 mm .16 in.
Total height	ISO 1765 / BS 4051	7.0 mm .28 in.
Pile weight		450 g/m ² 13.3 oz/yd ² (+/- 7.5%)
Total weight	ISO 8543 / BS 4223 Clause 7	2710 g/m ² 79.8 oz/yd ² (+/- 7.5%)
Number of tufts	ISO 1763 / BS 4223 Clause 6	65500 1/m ² 55000 1/yd ²
Roll width	ISO 3018 / BS 5921	90 120cm

Performances:

Walking test	EN 1815 / ISO TR 6356 / DD68
Dimensional Stability	EN 986 / ISO 2551 / DIN 54318
Electrical resistivity	IBM / ICL
Electrical resistivity vertical	DIN 54345
Electrical resistivity horizontal	DIN 54345
Sound insulation	ISO 140-8 / BS 3638
Thermal retention	ISO 8302 / DIN 52612
Soiling (dry / wet)	EN 1269
Colour Fastness:	
To light	ISO 105 B02 / DIN 54004 / BS 1006
To water	ISO 105 E01 / DIN 54006 / BS 1006
To seawater	ISO 105 E02 / DIN 54007 / BS 1006
To shampoo	BS 1006
To rubbing dry	ISO 105 X12 / DIN 54021 / BS 1006
wet	
Flammability rating:	
NBS Flooring Radiant Panel test	ASTM E648 / DIN 4102 / NEN 1775
Pill test	ISO 6925 = ASTM D2829 / BS 6307
Hot Metal Nut	BS 4790 / BS 5287
UK Radiant panel test	BS 476 (7)
Austrian Radiant panel test	Oenorm 3810 / Oenorm 3800 (1)
Kleimbrenner	DIN 54332 / NEN 1775 (1)
Panneau radiant	NF P-92-506

Continued on next page

United Kingdom

COBA Europe Ltd
 Marlborough Drive
 Fleckney, Leicestershire
 LE8 8UR

☎ +44 (0)116 240 1088
 ✉ sales@coba-europe.com
 🌐 www.coba-europe.com

Germany

COBA Europe GmbH
 Pullenweg 1 - 3
 41352 Korschenbroich

☎ +49 (2161) 2945-0
 ✉ verkauf@coba-europe.de
 🌐 www.coba-europe.de

Slovakia

COBA Europe s.r.o.
 Terchová - Vyšné Kamenec 11
 SK-013 06

☎ +421 41 507 11 12
 ✉ sales@coba-europe.sk
 🌐 www.coba-europe.sk

The information contained within this datasheet is for guidance only. The data and suggested application are not exhaustive. All dimensions quoted are nominal figures. Please note that some products may be subject to a degree of shrinkage when installed into some applications.

Gut certificate no.

European Overall Classification	EN 1307				
Strapazierwert	DIN 66095 (2)	Gering	Normal	Stark	Extrem
Komfortwert	DIN 66095 (2)	Einfach	Gut	Hoch	Luxurious
Flammability rating:					
NBS Flooring Radiant	ASTM E648/DIN 4102/NEN 1775	-			
Pill (Tablet) test	ISO 6925 = ASTM D2829/ BS 6307	-			
Hot Metal Nut	BS 4790/BS 5287			Low radius	
UK Radiant panel test	BS 476 (7)	-			
Austrian radiant panel test	Oenorm 3810 / Oenorm 3800 (1)	-			
Kleinbrenner	DIN 54332 / NEN 1775 (1)			Ta (B2)/T3	
Panneau radiant	NF P-92-506	-			

Gut certificate no.

20249

European Overall Classification EN 1307 2LC1

Strapazierwert DIN 66095 (2)

Komfortwert DIN 66095 (2)

End of document

United Kingdom

COBA Europe Ltd
Marlborough Drive
Fleckney, Leicestershire
LE8 8UR

+44 (0)116 240 1088
sales@cobaeeurope.com
www.cobaeeurope.com

Germany

COBA Europe GmbH
Pullenweg 1 - 3
41352 Korschenbroich

+49 (2161) 2945-0
verkauf@cobaeeurope.de
www.cobaeeurope.de

Slovakia

COBA Europe s.r.o.
Terchová - Vyšné Kamenec 11
SK-013 06

+421 41 507 11 12
sales@cobaeeurope.sk
www.cobaeeurope.sk

The information contained within this datasheet is for guidance only. The data and suggested application are not exhaustive. All dimensions quoted are nominal figures. Please note that some products may be subject to a degree of shrinkage when installed into some applications.