







EX260, Integrated Type (For Output) Serial Transmission System EX260-SEC2

Datasheet

- Centralised & compact serial transmission system for output
- Compatible protocols: Ethernet POWERLINK, PROFINET, EtherNet/IPTM, EtherCAT®, PROFIBUS DP, DeviceNetTM, CC-Link, IO-Link, CANopen, Modbus, AS-Interface
- Up to 32 solenoids, up to 24 stations
- Applicable valve series: new SY, VQC, S0700, SV
- Up to IP67 enclosure compliant.

Protocol	EC (EtherCAT)
Output Polarity/Communication Connector	2 [32 Outputs, COM (NPN), M12 Connector]
Maximum ambient temperature	50 °C
Minimum ambient temperature	−10 °C
General power supply	24 VDC
Conform to the European RoHS Directive	Conform
Approvals	CE marking, UL (CSA) compatible
Operating humidity range	35 to 85% RH (No condensation)
Type of electrical connector	M12
Version	Conformance Test Record V.1.1
Number of outputs	32
SI unit output polarity	Sink/NPN (Positive common)
Communication speed	100 Mbps
Enclosure	IP67
Weight	0.200 Kg

Dimensions



Additional information

Catalogue	EX260-C_EU.pdf
Declaration of conformity	newDoC_EX260_TF1V137EN-A.pdf
Installation manuals	IM_EX260-SIL1_SMW81EN.pdf IMM_EX260-SPNx-TFN34GB.pdf IMM_EX260-SDN_TFN21GB.pdf IMM_EX260-SENx_TFP47GB.pdf IMM_EX260-SMJx_TFP09GB.pdf IM_EX260-SPLx-SMW50EN.pdf IMM_EX260-SEC-TFN22GB.pdf
Operation manuals	quick-guide_EX260-SMJx_EN.pdf Quick-guide_EX260-SPNx_PROFINET_EN.pdf Quick-guide_EX260-SPLx_POWERLINK_EN.pdf OM_EX260-SPLx_POWERLINK_EN.pdf OM_EX260-SDNx_DeviceNet_EN-G.pdf OM_EX260-SPRx_PROFIBUS-DP_EN.pdf Quick-guide_EX260-SENx_EtherNetIP_EN.pdf OM_EX9_ZSW-IPC2_OMV1027EN-A.pdf Quick-guide_EX260-SDNx_DeviceNet_EN.pdf OM_EX260-SPNx_PROFINET_EN-D.pdf Quick-guide_EX260-SPRx_PROFIBUS-DP_EN.pdf OM_EX260-SIL1_IO-LinkEN.pdf OM_EX260-SECx_EtherCAT_EN-E.pdf OM_EX9_ZSW-IPC1_OMV1026EN-A.pdf OM_EX260-SMJx-CC-Link_EN-H.pdf OM_EX260-SECx_EtherNetIP_EN-D.pdf Quick-guide_EX260-SECx_EtherCAT_EN.pdf