

EVO-STIK MULTI-PURPOSE SILICONE SEALANT CLEAR
Supersedes Date: 10-Oct-2018

Revision date 01-May-2020
Revision Number 1.01

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product Identifier

Product Name EVO-STIK MULTI-PURPOSE SILICONE SEALANT CLEAR
Pure substance/mixture Mixture

1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended use Sealant.
Uses advised against None known

1.3. Details of the supplier of the safety data sheet

Company Name

Bostik Limited
Common Rd
ST16 3EH
Stafford UK
Tel: +44 (1785) 27 26 25
Fax: +44 (1785) 25 72 36

E-mail address SDS.box-EU@bostik.com

1.4. Emergency telephone number

United Kingdom +44 (1785) 272650
Ireland +353 (1) 8624900 (Monday- Friday 9am-5pm)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Regulation (EC) No 1272/2008

Not classified

2.2. Label Elements

Not classified

Signal word
None

Hazard statements
Not classified

EU Specific Hazard Statements

EUH208 - Contains 4,5-dichloro-2-octyl-2H-isothiazol-3-one [DCOIT]. May produce an allergic reaction.

Precautionary statements

P101 - If medical advice is needed, have product container or label at hand.
P102 - Keep out of reach of children.

2.3. Other Hazards

Small amounts of acetic acid (CAS 64-19-7) are formed by hydrolysis and released upon curing

SAFETY DATA SHEET

EVO-STIK MULTI-PURPOSE SILICONE SEALANT CLEAR
Supersedes Date: 10-Oct-2018

Revision date 01-May-2020
Revision Number 1.01

PBT & vPvB

This mixture contains no substance considered to be persistent, bioaccumulating or toxic (PBT) This mixture contains no substance considered to be very persistent nor very bioaccumulating (vPvB)

SECTION 3: Composition/information on ingredients

3.1 Substances

Not applicable

3.2 Mixtures

Chemical name	EC No	CAS No	Weight-%	Classification according to Regulation (EC) No. 1272/2008 [CLP]	Specific concentration limit (SCL)	REACH Registration Number
Hydrocarbons, C13-C23, n-alkanes, isoalkanes, cyclics, < 0.03% aromatics	932-078-5	--	>25 - <40	Asp. Tox. 1 (H304)		01-2119552497-29-xxxx
Triacetoxypropylsilane	241-816-9	17865-07-5	1 - <3	Skin Corr. 1B (H314) (EUH071)		01-2119966899-07-XXXX
Silanetriol, methyl-, triacetate	224-221-9	4253-34-3	1- <2.5	Skin Corr. 1C (H314) Acute Tox. 4 (H302) (EUH014)		01-2119962266-32-XXXX
4,5-dichloro-2-octyl-2H-isothiazol-3-one [DCOIT]	264-843-8	64359-81-5	0.01 - <0.05	Skin Corr. 1B (H314) Eye Dam. 1 (H318) Skin Sens. 1A (H317) Acute Tox. 4 (H302) Acute Tox. 2 (H330) Aquatic Acute 1 (H400) M=100 Aquatic Chronic 1 (410) M=10		--

Full text of H- and EUH-phrases: see section 16

Note: ^ indicates not classified, however, the substance is listed in section 3 as it has an OEL

This product does not contain candidate substances of very high concern at a concentration $\geq 0.1\%$ (Regulation (EC) No. 1907/2006 (REACH), Article 59)

SECTION 4: First aid measures

4.1. Description of first aid measures

SAFETY DATA SHEET

EVO-STIK MULTI-PURPOSE SILICONE SEALANT CLEAR
Supercedes Date: 10-Oct-2018

Revision date 01-May-2020
Revision Number 1.01

General advice	If medical advice is needed, have product container or label at hand. Show this safety data sheet to the doctor in attendance.
Inhalation	Remove to fresh air. IF exposed or concerned: Get medical advice/attention.
Eye contact	Rinse thoroughly with plenty of water for at least 15 minutes, lifting lower and upper eyelids. Consult a doctor.
Skin contact	Wash skin with soap and water. In the case of skin irritation or allergic reactions see a doctor.
Ingestion	Clean mouth with water. Do NOT induce vomiting. Drink 1 or 2 glasses of water. Never give anything by mouth to an unconscious person.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms No information available.

4.3. Indication of any immediate medical attention and special treatment needed

Note to doctors Treat symptomatically.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media Full water jet. Do not scatter spilled material with high pressure water streams.

5.2. Special hazards arising from the substance or mixture

Specific hazards arising from the chemical Thermal decomposition can lead to release of toxic and corrosive gases/vapours.

5.3. Advice for firefighters

Special protective equipment for fire-fighters Firefighters should wear self-contained breathing apparatus and full firefighting turnout gear. Use personal protection equipment.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions Ensure adequate ventilation. Avoid contact with skin, eyes or clothing.

Other information Ventilate the area. Prevent further leakage or spillage if safe to do so.

For emergency responders Use personal protection recommended in Section 8.

6.2. Environmental precautions

Environmental precautions Do not flush into surface water or sanitary sewer system. Do not allow to enter into soil/subsoil. See Section 12 for additional Ecological Information.

6.3. Methods and material for containment and cleaning up

Methods for containment Do not scatter spilled material with high pressure water streams.

Methods for cleaning up Take up mechanically, placing in appropriate containers for disposal.

SAFETY DATA SHEET

EVO-STIK MULTI-PURPOSE SILICONE SEALANT CLEAR
Supersedes Date: 10-Oct-2018

Revision date 01-May-2020
Revision Number 1.01

6.4. Reference to other sections

Reference to other sections See section 8 for more information. See section 13 for more information.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Advice on safe handling Ensure adequate ventilation. Use personal protective equipment as required. Avoid contact with skin, eyes or clothing.

General hygiene considerations Handle in accordance with good industrial hygiene and safety practice. Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Take off all contaminated clothing and wash it before reuse.

7.2. Conditions for safe storage, including any incompatibilities

Storage Conditions Keep container tightly closed in a dry and well-ventilated place. Keep away from food, drink and animal feedingstuffs.

7.3. Specific end use(s)

Specific Use(s)
Sealant.

Risk Management Methods (RMM) The information required is contained in this Safety Data Sheet.

Other information Observe technical data sheet.

SECTION 8: Exposure controls/Personal protection

8.1. Control parameters

Exposure Limits Small amounts of acetic acid (CAS 64-19-7) are formed by hydrolysis and released upon curing

Chemical name	European Union	Ireland	United Kingdom
Acetic acid 64-19-7	-	TWA: 10 ppm TWA: 25 mg/m ³ STEL: 20 ppm STEL: 50 mg/m ³	TWA: 10 ppm TWA: 25 mg/m ³ STEL: 20 ppm STEL: 50 mg/m ³

Derived No Effect Level (DNEL) No information available

Predicted No Effect Concentration (PNEC) No information available.

8.2. Exposure controls

Engineering controls Ensure adequate ventilation, especially in confined areas.

Personal Protective Equipment

Eye/face protection
Hand protection

Tight sealing safety goggles.

Wear protective gloves. Gloves must conform to standard EN 374. Ensure that the breakthrough time of the glove material is not exceeded. Refer to glove supplier for

SAFETY DATA SHEET

EVO-STIK MULTI-PURPOSE SILICONE SEALANT CLEAR
Supersedes Date: 10-Oct-2018

Revision date 01-May-2020
Revision Number 1.01

Skin and body protection information on breakthrough time for specific gloves.
Suitable protective clothing.

Environmental exposure controls No information available.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state Liquid
Appearance Paste
Colour clear
Odour Acetic acid
Odour threshold No information available

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	No data available	
Melting point / freezing point	No data available	
Boiling point / boiling range	301 °C	
Flash point	> 100 °C	
Evaporation rate	No data available	
Flammability (solid, gas)	Not applicable for liquids .	
Flammability Limit in Air		
Upper flammability or explosive limits	No data available	
Lower flammability or explosive limits	No data available	
Vapour pressure	No data available	
Vapour density	No data available	
Relative density	No data available	
Water solubility	Immiscible in water	
Solubility(ies)	No data available	
Partition coefficient	No data available	
Autoignition temperature	No data available	
Decomposition temperature	No data available	
Kinematic viscosity	> 21 mm ² /s	@ 40°C
Dynamic viscosity	No data available	
Explosive properties	No data available	
Oxidising properties	No data available	

9.2. Other information

Solid content (%) No information available
VOC Content (%) No information available
Density 0.97 g/cm³
Minimum Ignition Temperature (°C) 200

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity No information available.

10.2. Chemical stability

Stability Stable under normal conditions.

Explosion Data

Sensitivity to mechanical impact None.
Sensitivity to static discharge None.

SAFETY DATA SHEET

EVO-STIK MULTI-PURPOSE SILICONE SEALANT CLEAR
Supersedes Date: 10-Oct-2018

Revision date 01-May-2020
Revision Number 1.01

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions None under normal processing.

10.4. Conditions to avoid

Conditions to avoid None known based on information supplied.

10.5. Incompatible materials

Incompatible materials None known based on information supplied.

10.6. Hazardous decomposition products

Hazardous decomposition products None under normal use conditions. Stable under recommended storage conditions.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Information on likely routes of exposure

Product Information

Inhalation	Based on available data, the classification criteria are not met.
Eye contact	Based on available data, the classification criteria are not met.
Skin contact	Based on available data, the classification criteria are not met.
Ingestion	Based on available data, the classification criteria are not met.

Symptoms related to the physical, chemical and toxicological characteristics

Symptoms No information available.

Numerical measures of toxicity

Acute Toxicity

Component Information

Chemical name	Oral LD50	Dermal LD50	Inhalation LC50
Hydrocarbons, C13-C23, n-alkanes, isoalkanes, cyclics, < 0.03% aromatics --	LD50 > 5000 mg/kg (Rattus) OECD 401	LD50 > 2000 mg/kg (Oryctolagus cuniculus) OECD 402	
Silanetriol, methyl-, triacetate 4253-34-3	LD50 = 1600 mg/kg (Rattus) OECD 401		
4,5-dichloro-2-octyl-2H-isothiaz ol-3-one [DCOIT] 64359-81-5	=1636 mg/kg (Rattus)	> 2000 mg/kg (Oryctolagus cuniculus)	=0.26 mg/L (Rattus) 4 h

Delayed and immediate effects as well as chronic effects from short and long-term exposure

SAFETY DATA SHEET

EVO-STIK MULTI-PURPOSE SILICONE SEALANT CLEAR
Supersedes Date: 10-Oct-2018

Revision date 01-May-2020
Revision Number 1.01

Skin corrosion/irritation The assessment of the result of testing was done in accordance with the guideline of the Commission 92/ 69/ EEC.

Serious eye damage/eye irritation By analogy to another tested similar product: No irritation after contact to the eyes. (H319 is void). The assessment of the result of testing was done in accordance with the guideline of the Commission 92/ 69/ EEC.

Respiratory or skin sensitisation Based on available data, the classification criteria are not met.

Component Information			
4,5-dichloro-2-octyl-2H-isothiazol-3-one [DCOIT] (64359-81-5)			
Method	Species	Exposure route	Results
OECD Test No. 406: Skin Sensitisation	Guinea pig		sensitising

Germ cell mutagenicity Based on available data, the classification criteria are not met.

Carcinogenicity Based on available data, the classification criteria are not met.

Reproductive toxicity Based on available data, the classification criteria are not met.

STOT - single exposure Based on available data, the classification criteria are not met.

STOT - repeated exposure Based on available data, the classification criteria are not met.

Aspiration hazard Based on available data, the classification criteria are not met.

SECTION 12: Ecological information

12.1. Toxicity

Ecotoxicity

Chemical name	Algae/aquatic plants	Fish	Toxicity to Micro-organisms	Crustacea	M-Factor	M-Factor (long-term)
Hydrocarbons, C13-C23, n-alkanes, isoalkanes, cyclics, < 0.03% aromatics --	EL50 (72h) > 1000 mg/L (Skeletonema costatum)	LL50 (96h) > 1028 mg/L (Scophthalmus maximus)	-	LL50 (48h) > > 3193 mg/l (Acartia tonsa)		
4,5-dichloro-2-octyl-2H-isothiazol-3-one [DCOIT] 64359-81-5	EC50 (72h) =0.025 mg/L Algae (Scenedesmus subspicatus)(OECD 201)	LC50 (96h) 0.0078 mg/L (Oncorhynchus mykiss)(OECD 203)	-	EC50 (48h) 0.0097 mg/L Daphnia magna (OECD 202)	100	10

12.2. Persistence and degradability

Persistence and degradability No information available.

SAFETY DATA SHEET

EVO-STIK MULTI-PURPOSE SILICONE SEALANT CLEAR
Supersedes Date: 10-Oct-2018

Revision date 01-May-2020
Revision Number 1.01

Component Information			
4,5-dichloro-2-octyl-2H-isothiazol-3-one [DCOIT] (64359-81-5)			
Method	Exposure time	Value	Results
OECD Test No. 308: Aerobic and Anaerobic Transformation in Aquatic Sediment Systems		Half-life	1.1-1.3 days

12.3. Bioaccumulative potential

Bioaccumulation There is no data for this product.

Component Information

Chemical name	Partition coefficient	Bioconcentration factor (BCF)
4,5-dichloro-2-octyl-2H-isothiazol-3-one [DCOIT] 64359-81-5	4.4	13

12.4. Mobility in soil

Mobility in soil No information available.

12.5. Results of PBT and vPvB assessment

PBT and vPvB assessment . The components in this formulation do not meet the criteria for classification as PBT or vPvB.

Chemical name	PBT and vPvB assessment
Triacetoxypropylsilane 17865-07-5	The substance is not PBT / vPvB
Silanetriol, methyl-, triacetate 4253-34-3	The substance is not PBT / vPvB
4,5-dichloro-2-octyl-2H-isothiazol-3-one [DCOIT] 64359-81-5	The substance is not PBT / vPvB

12.6. Other adverse effects

Other adverse effects No information available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Waste from residues/unused products Dispose of contents/container in accordance with local, regional, national, and international regulations as applicable.

Contaminated packaging Do not reuse empty containers. Handle contaminated packages in the same way as the product itself.

Other information Waste codes should be assigned by the user based on the application for which the product was used.

SECTION 14: Transport information

Land transport (ADR/RID)

14.1 UN Number Not regulated

14.2 Proper Shipping Name Not regulated

SAFETY DATA SHEET

EVO-STIK MULTI-PURPOSE SILICONE SEALANT CLEAR
Supersedes Date: 10-Oct-2018

Revision date 01-May-2020
Revision Number 1.01

14.3 Transport hazard class(es) Not regulated
14.4 Packing Group Not regulated
14.5 Environmental hazards Not applicable
14.6 Special Provisions None

IMDG

14.1 UN number Not regulated
14.2 Proper Shipping Name Not regulated
14.3 Transport hazard class(es) Not regulated
14.4 Packing group Not regulated
14.5 Marine Pollutant Np
14.6 Special Provisions None
14.7 Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code Not applicable

Air transport (ICAO-TI / IATA-DGR)

14.1 UN number Not regulated
14.2 Proper Shipping Name Not regulated
14.3 Transport hazard class(es) Not regulated
14.4 Packing group Not regulated
14.5 Environmental hazards Not applicable
14.6 Special Provisions None

Section 15: REGULATORY INFORMATION

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

European Union

Take note of Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work

Check whether measures in accordance with Directive 94/33/EC for the protection of young people at work must be taken.

Take note of Directive 92/85/EC on the protection of pregnant and breastfeeding women at work

Registration, Evaluation, Authorization, and Restriction of Chemicals (REACH) Regulation (EC 1907/2006)

SVHC: Substances of Very High Concern for Authorisation:

This product does not contain candidate substances of very high concern at a concentration $\geq 0.1\%$ (Regulation (EC) No. 1907/2006 (REACH), Article 59)

EU-REACH (1907/2006) - Annex XVII - Substances subject to Restriction

This product does not contain substances subject to restriction (Regulation (EC) No. 1907/2006 (REACH), Annex XVII).

Substance subject to authorisation per REACH Annex XIV

This product does not contain substances subject to authorisation (Regulation (EC) No. 1907/2006 (REACH), Annex XIV)

Ozone-depleting substances (ODS) regulation (EC) 1005/2009

Not applicable

Persistent Organic Pollutants

Not applicable

SAFETY DATA SHEET

EVO-STIK MULTI-PURPOSE SILICONE SEALANT CLEAR
Supersedes Date: 10-Oct-2018

Revision date 01-May-2020
Revision Number 1.01

15.2. Chemical safety assessment

Chemical Safety Assessments have been carried out by the Reach registrants for substances registered at >10 tpa. No Chemical Safety Assessment has been carried out for this mixture

SECTION 16: Other information

Key or legend to abbreviations and acronyms used in the safety data sheet

Full text of H-Statements referred to under section 3

EUH014 - Reacts violently with water
EUH071 - Corrosive to the respiratory tract
H302 - Harmful if swallowed
H304 - May be fatal if swallowed and enters airways
H314 - Causes severe skin burns and eye damage
H317 - May cause an allergic skin reaction
H318 - Causes serious eye damage
H330 - Fatal if inhaled
H400 - Very toxic to aquatic life

Legend

TWA	TWA (time-weighted average)
STEL	STEL (Short Term Exposure Limit)
Ceiling	Ceiling Limit Value
*	Skin designation
SVHC	Substance(s) of Very High Concern
PBT	Persistent, Bioaccumulative, and Toxic (PBT) Chemicals
vPvB	Very Persistent and very Bioaccumulative (vPvB) Chemicals
STOT RE	Specific target organ toxicity - Repeated exposure
STOT SE	Specific target organ toxicity - Single exposure
EWC	European Waste Catalogue

Key literature references and sources for data

No information available

Prepared By Product Safety & Regulatory Affairs

Revision date 01-May-2020

Indication of changes

Revision note Not applicable.

Training Advice No information available

Further information No information available

This material safety data sheet complies with the requirements of Regulation (EC) No. 1907/2006

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet