


06800050

RCK 80 - Self centring

2D Technical Drawing

Dynamic 3D View
Technical Specifications

Part number (CODE)	06800050
Ød (DD) mm	50
ØD (D) mm	65
D1 (D1) mm	86
D2 (D2) mm	92
L1 (L1) mm	45
L2 (L2) mm	62.5
L3 (L3) mm	71.0
L (L) mm	79.0
Maximum torque Mt (MT) Nm	2100
Clamping pressure - Shaft (CPS) N/mm ²	100
Clamping pressure - Hub (CPH) N/mm ²	75
Clamping screws DIN 912 MAT. 12.9 - Num. (CSN)	8
Clamping screws DIN 912 MAT. 12.9 - Type (CST)	M8x22
Clamping screws DIN 912 MAT. 12.9 - Torque (CSTQ) Nm	41.0