


**Part Number :** 5011894010

**Product Description :** 1.00mm Pitch, Pico-Clasp Low-Halogen Receptacle Crimp Housing, Dual Row, Inner Positive Lock, 40 Circuits, White

**Series Number :** 501189

**Status :** Active

**Product Category :** Connector Housings



## Documents & Resources

### Drawings

[5011894010\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[5011894010.dxf](#)

### Specifications

[5011890000-AS-000.pdf](#)

[5011890000-AS-001.pdf](#)

[SPK-501189-001-001.pdf](#)

[5011890000-PS-001.pdf](#)

[5011890000-PS-002.pdf](#)

[5011891000-PS-001.pdf](#)

[5011891000-PS-002.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21

REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	Connector Housings
Series	501189
Description	1.00mm Pitch, Pico-Clasp Low-Halogen Receptacle Crimp Housing, Dual Row, Inner Positive Lock, 40 Circuits, White
Application	Signal, Wire-to-Board
Product Name	Pico-Clasp
UPC	822348789757

### Agency

UL	E29179
----	--------

### Physical

Breakaway	No
Circuits (maximum)	40

Color - Resin	White
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	261.100/mg
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.00mm
Pitch - Termination Interface	1.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
Pico-Clasp Vertical, Dual Row, Surface Mount Headers	<u><a href="#">203564</a></u>
Pico-Clasp Vertical, Dual Row, Surface Mount Headers	<u><a href="#">203565</a></u>
Pico-Clasp Vertical Dual Row Headers	<u><a href="#">501190</a></u>
Pico-Clasp Right-Angle, Dual Row, Surface Mount Headers	<u><a href="#">203566</a></u>
Pico-Clasp Right-Angle, Dual Row, Surface Mount Headers	<u><a href="#">203567</a></u>
Pico-Clasp Right-Angle Dual Row Headers	<u><a href="#">501571</a></u>
Pico-Clasp Vertical, Dual Row, Surface Mount, Low-Halogen Headers	<u><a href="#">208391</a></u>
Pico-Clasp Right-Angle, Dual Row, Surface Mount, Low-Halogen	<u><a href="#">208393</a></u>

Headers	
---------	--

## Use with Part(s)

Description	Part Number
Pico-Clasp Female Crimp Terminals	<u>501193</u>

---

## Application Tooling

### Global

Description	Part Number
Extraction Tool for Pico-Clasp Wire-to-Board Terminals, 32-28 AWG	<u>638131700</u>

---

This document was generated on Aug 08, 2025