

SACB-DT-DBM-CAN-L-IV - Distributor box



1531886

<https://www.phoenixcontact.com/fr/products/1531886>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Distributor box, application: Mobile hydraulics, connection method: DT04 connector, number of slots: 6, number of positions: 4, status display: yes, CAN Bus/DeviceNet

Commercial data

Item number	1531886
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AF2IED
Product key	AF2IED
GTIN	4067923000131
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	290 g
Customs tariff number	85366990
Country of origin	Country of origin will be provided upon delivery.

SACB-DT-DBM-CAN-L-IV - Distributor box



1531886

<https://www.phoenixcontact.com/fr/products/1531886>

Technical data

Notes

Assembly note	NOTE: Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties.
Note on application	2x M5 (#10) screws. Torque: 2.4 Nm (21 lb _f -in.) maximum (not included)

Product properties

Application	Mobile hydraulics
Number of positions	4
Number of slots	6
LED	yes

System properties

Local diagnostics

Monitored function	Supply voltage
Optical representation	Blue LED

Electrical properties

Max. operating voltage U_{max}	32 V DC
Local diagnostics	Supply voltage Blue LED
Max. current carrying capacity per path	13 A (Battery)
Current carrying capacity per slot	42 A (8 A maximum for signals, 13 A maximum for power)

Connection data

Conductor connection

Sensor/actuator connection system	DT04 connector
-----------------------------------	----------------

Signaling

Status display present	yes
------------------------	-----

Dimensions

Dimensional drawing	
Width	51 mm
Height	33 mm
Length	238 mm

SACB-DT-DBM-CAN-L-IV - Distributor box



1531886

<https://www.phoenixcontact.com/fr/products/1531886>

Material specifications

Contact material	Cu alloy
Contact surface material	Ni
Contact carrier material	PA 66 GF

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67 (when using Phoenix Contact connection cables)
Ambient temperature (operation)	-40 °C ... 85 °C

SACB-DT-DBM-CAN-L-IV - Distributor box




1531886

<https://www.phoenixcontact.com/fr/products/1531886>


Drawings

Dimensional drawing



Dimensional drawing

Schematic diagram



DEUTSCH DT04-4P pin assignment


SACB-DT-DBM-CAN-L-IV - Distributor box

1531886

<https://www.phoenixcontact.com/fr/products/1531886>



Circuit diagram



SACB-DT-DBM-CAN-L-IV - Distributor box



1531886

<https://www.phoenixcontact.com/fr/products/1531886>

Classifications

ECLASS

ECLASS-15.0	27440116
ECLASS-13.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACB-DT-DBM-CAN-L-IV - Distributor box



1531886

<https://www.phoenixcontact.com/fr/products/1531886>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT SAS
52 Boulevard de Beaubourg Emerainville
77436 Marne La Vallée Cedex 2 France
+33 (0) 1 60 17 98 98
documentation@phoenixcontact.fr