


TECHNICAL FILE

SWEDISH PIPE WRENCHES



EGA Master Swedish Pipe Wrenches SERIE MASTER Cr-V are manufactured with a chrome-vanadium alloy and fulfill the DIN 5234 standard. They are totally forged.

Thanks to its exterior design, they are perfect for use in places with difficult access. The jaws design and the teeth orientation provide an ideal grip of the pipe.

The soft foam coated handles provide a great and comfortable use..



SWEDISH PIPE WRENCH S 45°




DIN 5234

COD	L	A	B	C	Kg.
61010	235	15	1/2"	8.8	0.40
61011	330	20	1"	13	0.79
61012	425	26	1.1/2"	14	1.43
61013	535	28	2"	16	2.37
61022	648	35	3"	19	4.16

Cr-V

SWEDISH PIPE WRENCH 45°





DIN 5234

COD	L	A	B	C	Kg.
61040	235	18	1/2"	8.8	0.42
61041	330	24	1"	13	0.75
61042	425	27	1.1/2"	14	1.40
61043	535	33	2"	16	2.32

Cr-V

SWEDISH PIPE WRENCH 90°





DIN 5234

COD	L	A	B	C	Kg.
61046	320	18	1"	15	0.73
61047	432	20	1.1/2"	18	1.31
61048	560	25	2"	20	2.32
61049	620	30	3"	20	2.97

Cr-V

FITTINGS WRENCH





DIN 5234

COD	L	A	B	C	Kg.	
61050	315	21	1"	9.5	0.79	64257

Cr-V

SWEDISH PIPE WRENCH STRAIGHT JAWS



DIN 5234					
COD	← L →	← A →	← B →	← C →	Kg. 
60963	320	24	1"	13	0.75
60964	420	27	1.1/2"	14	1.40
60965	560	33	2"	16	2.32

Cr-V