

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
IJ	—		A	INITIAL ISSUE	10 SEP 05	MGR	DB

D

C

B


A

D

C

B

A



NOTES:

- 1 ATTENUATION $\leq 0,3$ dB, MEASURED AT 1300nm ACC. TO IEC 61300–3–4 EQUILIBRIUM MODE CONDITION
- 2 SUPPLY FILLED OUT TEST RESULT SHEET WITH EACH INDIVIDUALLY PACKED ASSEMBLY
- 3 CABLE INFO:

CORE DIA

— 62,5/125 μm

OUTER DIA

— 2,5 mm

JACKET COLOR

— ORANGE

JACKET MATERIAL

— LSZH

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (Meter)
X-5349573-Y	XY,0
9-5349573-1	1,5
9-5349573-8	15,5
9-5349573-9	9,5
0-5349573-0	100,0

1	—	TEST RESULT SHEET	—
2	—	PROTECTIVE COVER, 2.5MM, BLACK	5
2	—	KIT, MM, CER, ASSY, BULK	4
2	—	CRIMP EYELET, BRIGHT TIN	3
2	—	FOAC STRAIN RELIEF 2,5 BAY BLACK	2
L	—	FOCAB 62.5/125 SIMPLEX, ORANGE	1
Qty	Part Number	Description	Item
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 10 SEP 05 CHK 10 SEP 05 APVD 10 SEP 05 PRODUCT SPEC APPLICATION SPEC WEIGHT — CUSTOMER DRAWING	GIRIYAPPA. M DIWAKAR BELAVADI DIWAKAR BELAVADI FOMM62,5 LEAD 2,5S ST - ST A200779C=5349573 SCALE NTS SHEET 1 OF 1 REV A
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH —	tyco Electronics Tyco Electronics Corporation FOBU, Bangalore, India
MATERIAL —		RESTRICTED TO —	