


R76_125C, Film, Double Metallized Polypropylene, General Purpose, 0.015 uF, 5%, 630 VDC, 105°C, Lead Spacing = 10mm



Dimensions

L	13mm +0.2mm
H	12mm +0.1mm
T	6mm +0.2mm
S	10mm +/-0.4mm
LL	25mm +2/-1mm
F	0.6mm +/-0.05mm

Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	1200

General Information

Series:	R76_125C
Dielectric:	Double Metallized Polypropylene
Style:	Radial
Features:	Automotive Grade, Pulse
RoHS:	Yes
Lead:	Wire Leads
Qualifications:	AEC-Q200
AEC-Q200:	Yes

Specifications

Capacitance:	0.015 uF
Capacitance Tolerance:	5%
Voltage AC:	400 VAC
Voltage DC:	630 VDC
Temperature Range:	-55/+125°C
Rated Temperature:	105°C
Dissipation Factor:	0.03% 1kHz, 0.04% 10kHz, 0.1% 100kHz
Insulation Resistance:	100 GOhms
Max dV/dt:	4000 V/us
Resistance:	127.32 mOhms (25kHz)
Ripple Current:	0.94 Amps (25kHz 60C), 60 Amps (Peak)
Inductance:	9 nH