

# MAXI-ROLL

BLUE RESILEX® P WHEEL



## STRONG POINTS

- Low starting effort.
- Non-marking tyre.
- 3 year bonding guarantee.
- High degree of resistance to abrasion.



As an optional extra: "Directional lock" DL for MAXI-ROLL code: 200 2000

## APPLICATIONS

*Flexible and easy materials handling on all types of industrial surface, even those in poor condition.*

*Does not leave scratches or other marks on surfaces, has a high degree of resistance to abrasion.*

**CASTOR ASSEMBLY:** • Swivel or fixed. • Pressed steel. • Fastening by top plate. • Swivels on two rows of balls. • Bright zinc-plated protection.

**WHEEL:** • blue Resilex® P: super-elastic blue rubber tyre bonded onto the black polyamide-6 centre. • Precision ball bearings. • Bolted axle.

**LOCKING:** • **SR** Stop-roll: double-action adjustable front brake: wheel and swivel. • Steel pedal.

**OPTION :** • Directional lock to be fastened onto the castor's top plate in order to momentarily transform a swivel castor into a fixed one.

										Type			Code	EAN 13
<b>125</b>									<b>300</b>			1,895	<b>138 7232</b>	339680 622051 1
												2,240	<b>1 381 7232</b>	339680 622053 5
												1,235	<b>520 7232</b>	339680 622055 9
<b>160</b>									<b>400</b>			2,315	<b>138 7233</b>	339680 622071 9
												2,635	<b>1 381 7233</b>	339680 622073 3
												1,560	<b>520 7233</b>	339680 622075 7
<b>200</b>									<b>400</b>			2,700	<b>138 7234</b>	339680 622091 7
												3,065	<b>1 381 7234</b>	339680 622093 1
												2,185	<b>520 7234</b>	339680 622095 5
<b>250</b>									<b>350</b>			3,625	<b>138 7235</b>	339680 622113 6
												3,990	<b>1 381 7235</b>	339680 622115 0
												3,485	<b>520 7235</b>	339680 622116 7

300  
400  
daN