



SAFETY DATA SHEET Janitol Multiclean

According to Regulation (EU) No 453/2010

SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product identifier

Product name Janitol Multiclean
Product No. JMC60T, JMC60TIS, JMC76S, JMC90J

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Detergent. . For full details regarding recommended uses please refer to the product label.

1.3. Details of the supplier of the safety data sheet

Supplier Deb Ltd
Denby Hall Way
Denby
Derbyshire
DE5 8JZ
Main Tel. 01773 855100
Technical Tel 01773 855105
reach@deb.co.uk

1.4. Emergency telephone number

National Poisons Information Service (UK) 0844 8920111

SECTION 2: HAZARDS IDENTIFICATION

2.1. Classification of the substance or mixture

Classification (1999/45/EEC) Xi;R36/37/38.

Environment

The product does not meet the requirement for classification as an environmental hazard in accordance with directive 1999/45/EEC

2.2. Label elements

Detergent Labelling

5 - < 15% phosphates
< 5% non-ionic surfactants
amphoteric surfactants
anionic surfactants

Labelling



Irritant

Risk Phrases

R36/37/38

Irritating to eyes, respiratory system and skin.

Safety Phrases

S2

Keep out of the reach of children.

S24/25

Avoid contact with skin and eyes.

S26

In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.

S37

Wear suitable gloves.

S46

If swallowed, seek medical advice immediately and show this container or label.

Janitol Multiclean

S51

Use only in well-ventilated areas.

S64

If swallowed, rinse mouth with water (only if the person is conscious).

2.3. Other hazards

This product does not contain any PBT or vPvB substances.

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS**3.2. Mixtures**

TETRAPOTASSIUM PYROPHOSPHATE		5-10%
CAS-No.: 7320-34-5	EC No.: 230-785-7	Registration Number: 01-2119489369-18-xxxx
Classification (EC 1272/2008) Eye Irrit. 2 - H319	Classification (67/548/EEC) Xi;R36.	
2-AMINOETHANOL		5-10%
CAS-No.: 141-43-5	EC No.: 205-483-3	
Classification (EC 1272/2008) Acute Tox. 4 - H302 Acute Tox. 4 - H312 Acute Tox. 4 - H332 Skin Corr. 1B - H314 STOT SE 3 - H335	Classification (67/548/EEC) C;R34 Xn;R20/21/22	
ISOTRIDECANOL, ETHOXYLATED 6.5 MOL EO		1-5%
CAS-No.: 69011-36-5	EC No.:	
Classification (EC 1272/2008) Acute Tox. 4 - H302 Eye Dam. 1 - H318	Classification (67/548/EEC) Xn;R22. Xi;R41.	

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

SECTION 4: FIRST AID MEASURES**4.1. Description of first aid measures****Inhalation**

Move the exposed person to fresh air at once. Get medical attention if any discomfort continues.

Ingestion

NEVER MAKE AN UNCONSCIOUS PERSON VOMIT OR DRINK FLUIDS! Rinse mouth thoroughly. Get medical attention.

Skin contact

Remove affected person from source of contamination. Remove contaminated clothing. Wash the skin immediately with soap and water. Get medical attention if irritation persists after washing.

Eye contact

Remove victim immediately from source of exposure. Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes and get medical attention.

4.2. Most important symptoms and effects, both acute and delayed**Inhalation**

Irritation of nose, throat and airway.

Ingestion

May cause discomfort if swallowed. May cause stomach pain or vomiting.

Skin contact

Skin irritation.

Janitol Multiclean

Eye contact

Irritation of eyes and mucous membranes.

4.3. Indication of any immediate medical attention and special treatment needed

No recommendation given, but first aid may still be required in case of accidental exposure, inhalation or ingestion of this chemical. If in doubt, GET MEDICAL ATTENTION PROMPTLY!

SECTION 5: FIREFIGHTING MEASURES

5.1. Extinguishing media

Extinguishing media

This product is not flammable. Use fire-extinguishing media appropriate for surrounding materials.

5.2. Special hazards arising from the substance or mixture

Hazardous combustion products

None under normal conditions.

5.3. Advice for firefighters

Special Fire Fighting Procedures

No specific fire fighting procedure given.

Protective equipment for fire-fighters

Wear full protective clothing.

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

Wear protective clothing as described in Section 8 of this safety data sheet.

6.2. Environmental precautions

Collect and dispose of spillage as indicated in section 13. Avoid discharge to the aquatic environment.

6.3. Methods and material for containment and cleaning up

Stop leak if possible without risk. Absorb in vermiculite, dry sand or earth and place into containers. Flush with plenty of water to clean spillage area. Do not let washing down water contaminate ponds or waterways.

6.4. Reference to other sections

For personal protection, see section 8. For waste disposal, see section 13.

SECTION 7: HANDLING AND STORAGE

7.1. Precautions for safe handling

Avoid spilling, skin and eye contact.

7.2. Conditions for safe storage, including any incompatibilities

Store in closed original container at temperatures between 0°C and 40°C.

Storage Class

Chemical storage.

7.3. Specific end use(s)

The identified uses for this product are detailed in Section 1.2.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. Control parameters

Name	STD	TWA - 8 Hrs		STEL - 15 Min		Notes
2-AMINOETHANOL	WEL	1 ppm	2,5 mg/m ³	3 ppm	7,6 mg/m ³	Sk

WEL = Workplace Exposure Limit.

Sk = Can be absorbed through skin.

Ingredient Comments

EU = Indicative Values according to Commission Directive 91/322/EEC.

Janitol Multiclean

TETRAPOTASSIUM PYROPHOSPHATE (CAS: 7320-34-5)**DNEL**

Professional	Inhalation.	Long Term	Systemic Effects	2.79 mg/m3
Consumer	Inhalation.	Long Term	Systemic Effects	0.68 mg/m3

PNEC

Freshwater	0.05	mg/l
Marinewater	0.005	mg/l
Freshwater	0.5	mg/l
STP	50	mg/l

8.2. Exposure controls**Protective equipment****Engineering measures**

Provide adequate ventilation.

Respiratory equipment

No specific recommendation made, but respiratory protection may still be required under exceptional circumstances when excessive air contamination exists.

Hand protection

Use suitable protective gloves if risk of skin contact. The most suitable glove must be chosen in consultation with the gloves supplier, who can inform about the breakthrough time of the glove material.

Eye protection

If risk of splashing, wear safety goggles or face shield.

Other Protection

Wear appropriate clothing to prevent any possibility of skin contact.

Hygiene measures

DO NOT SMOKE IN WORK AREA! Wash hands at the end of each work shift and before eating, smoking and using the toilet. Wash promptly if skin becomes wet or contaminated. Promptly remove any clothing that becomes contaminated. When using do not eat, drink or smoke.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES**9.1. Information on basic physical and chemical properties**

Appearance	Liquid
Colour	Yellow.
Odour	Characteristic.
Solubility	Soluble in water.
Initial boiling point and boiling range (°C)	
Not determined.	
Melting point (°C)	
Not determined.	
Relative density	1.039-1.059 25 C
Vapour density (air=1)	
Not determined.	
Vapour pressure	
Not determined.	
Evaporation rate	
Not determined.	
pH-Value, Conc. Solution	12-13
Viscosity	
Not determined.	
Decomposition temperature (°C)	
Not determined.	
Odour Threshold, Lower	
Not determined.	
Odour Threshold, Upper	
Not determined.	

Janitol Multiclean

Flash point (°C)

Not determined.

Auto Ignition Temperature (°C)

Scientifically unjustified.

Flammability Limit - Lower(%)

Scientifically unjustified.

Flammability Limit - Upper(%)

Scientifically unjustified.

Partition Coefficient

(N-Octanol/Water)

Scientifically unjustified.

Explosive properties

Scientifically unjustified.

Oxidising properties

Does not meet the criteria for oxidising.

9.2. Other information

Not relevant

SECTION 10: STABILITY AND REACTIVITY

10.1. Reactivity

Reaction with: Acids.

10.2. Chemical stability

Stable under normal temperature conditions.

10.3. Possibility of hazardous reactions

Not applicable.

10.4. Conditions to avoid

Avoid excessive heat for prolonged periods of time. Avoid frost.

10.5. Incompatible materials

Materials To Avoid

Strong acids.

10.6. Hazardous decomposition products

None under normal conditions.

SECTION 11: TOXICOLOGICAL INFORMATION

11.1. Information on toxicological effects

Acute toxicity:

Based on available data the classification criteria are not met.

Skin Corrosion/Irritation:

Slightly irritating.

Serious eye damage/irritation:

Based on available data the classification criteria are not met.

Respiratory or skin sensitisation:

Based on available data the classification criteria are not met.

Germ cell mutagenicity:

Based on available data the classification criteria are not met.

Carcinogenicity:

Does not contain any substances known to be carcinogenic.

Reproductive Toxicity:

Janitol Multiclean

Does not contain any substances known to be toxic to reproduction.

Specific target organ toxicity - single exposure:

Not classified as a specific target organ toxicant after a single exposure.

Specific target organ toxicity - repeated exposure:

Not classified as a specific target organ toxicant after repeated exposure.

Aspiration hazard:

Not anticipated to present an aspiration hazard based on chemical structure.

Inhalation

May cause irritation to the respiratory system.

Ingestion

May cause discomfort if swallowed.

Skin contact

Irritating to skin.

Eye contact

Irritating to eyes.

Toxicological information on ingredients.

2-AMINOETHANOL (CAS: 141-43-5)

Acute toxicity:

Acute Toxicity (Oral LD50)

1515 mg/kg Rat

Acute Toxicity (Dermal LD50)

1025 mg/kg Rabbit

ISOTRIDECANOL, ETHOXYLATED 6.5 MOL EO (CAS: 69011-36-5)

Toxic Dose 1 - LD 50

>300-2000 mg/kg (oral rat)

Acute toxicity:

Acute Toxicity (Dermal LD50)

> 2000 mg/kg Rat

TETRAPOTASSIUM PYROPHOSPHATE (CAS: 7320-34-5)

Toxic Dose 1 - LD 50

2.000 mg/kg (oral rat)

Acute toxicity:

Acute Toxicity (Dermal LD50)

> 2.0 mg/kg Rabbit

SECTION 12: ECOLOGICAL INFORMATION

Ecotoxicity

The product components are not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment. The product does not meet the requirement for classification as an environmental hazard in accordance with directive 1999/45/EEC

12.1. Toxicity

The product does not meet the requirement for classification as an environmental hazard in accordance with directive 1999/45/EEC

12.2. Persistence and degradability

Degradability

The surfactant(s) contained in this preparation complies(comply) with the biodegradability criteria as laid down in Regulation (EC) No.648/2004 on detergents. Data to support this assertion are held at the disposal of the competent authorities of the Member States and will be made available to them, at their direct request or at the request of a detergent manufacturer.

Janitol Multiclean

12.3. Bioaccumulative potential**Bioaccumulative potential**

No data available on bioaccumulation.

Partition coefficient

Scientifically unjustified.

12.4. Mobility in soil**Mobility:**

The product is soluble in water. The product is non-volatile.

12.5. Results of PBT and vPvB assessment

None known.

12.6. Other adverse effects

None known.

SECTION 13: DISPOSAL CONSIDERATIONS**General information**

Waste to be treated as controlled waste. Disposal to licensed waste disposal site in accordance with local Waste Disposal Authority.

13.1. Waste treatment methods

Dispose of waste and residues in accordance with local authority requirements. No specific disposal method required. Recover and reclaim or recycle, if practical.

SECTION 14: TRANSPORT INFORMATION

Road Transport Notes Not Classified

Rail Transport Notes Not classified.

Sea Transport Notes Not classified.

14.1. UN number

Not applicable.

14.2. UN proper shipping name

Not applicable.

14.3. Transport hazard class(es)

Not applicable.

14.4. Packing group

Not applicable.

14.5. Environmental hazards**Environmentally Hazardous Substance/Marine Pollutant**

No.

14.6. Special precautions for user

Not applicable.

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Not applicable.

SECTION 15: REGULATORY INFORMATION**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

Janitol Multiclean

EU Legislation

Dangerous Substance Directive 67/548/EEC. Dangerous Preparations Directive 1999/45/EC. Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments. Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006 with amendments.

15.2. Chemical Safety Assessment

No chemical safety assessment has been carried out.

SECTION 16: OTHER INFORMATION

General information

Only trained personnel should use this material.

Revision Comments

New REACH Annex 2 Compliant MSDS

Revision Date 30/01/2013

Revision 3

Supersedes date 04/08/2011

Risk Phrases In Full

R34	Causes burns.
R20/21/22	Harmful by inhalation, in contact with skin and if swallowed.
R22	Harmful if swallowed.
R36/37/38	Irritating to eyes, respiratory system and skin.
R36	Irritating to eyes.
R37	Irritating to respiratory system.
R41	Risk of serious damage to eyes.

Hazard Statements In Full

H302	Harmful if swallowed.
H312	Harmful in contact with skin.
H314	Causes severe skin burns and eye damage.
H315	Causes skin irritation.
H318	Causes serious eye damage.
H319	Causes serious eye irritation.
H332	Harmful if inhaled.
H335	May cause respiratory irritation.

Notes for Risk Phrases and Hazard Statements in Full

The full text for Risk Phrases and Hazard Statements in section 16 relates to the reference numbers in sections 2 and 3 and not necessarily the finished product classification.

Disclaimer

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.