

## FEATURES

- Contact rating 20A 125-250Vac
- Full Shield
- Orange cast iron body and pedal with sturdy aluminum shield for added protection
- Rated to IP56
- M20 cable entry

## RS PRO Momentary Heavy Duty Foot Switch - Cast Iron Case Material, DP-CO, 20 A @ 250 V ac Contact Current, 250V Contact

RS Stock No.: 116-827



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description ATTRIBUTE 1

RS PRO heavy duty foot switches which are ideal for industrial applications. The rugged cast metal construction is heavy enough to prevent the foot switch from sliding when being operated. The three holes on the switch lets you mount it to the floor or equipment. These foot switches also come with a shield for added protection.

This range of foot pedal switches includes:

116-827 – Momentary, DPDT

116-833 - Momentary, SPDT, Anti trip

116-849 - Momentary, SPDT

116-956 – Momentary, DPDT, Anti trip

## General Specifications

<b>Contact Configuration</b>	DP-CO
<b>Switch Operation</b>	Momentary
<b>Case Material</b>	Cast Iron
<b>Switch Environment</b>	Heavy Duty
<b>Guard Cover</b>	Yes
<b>Colour</b>	Orange
<b>Applications</b>	Foot switches are commonly used in applications where hands-free control is more practical or safer. They can be found on: Industrial machinery and smaller power tools, Hospital beds, Dentist Chairs, Lamps
<b>Cable Connection</b>	Single M20 cable entry

## Electrical Specifications

<b>Contact Voltage Rating (AC)</b>	250V
<b>Contact Current Rating</b>	20A @ 250V ac

## Mechanical Specifications

<b>Length</b>	228.6mm
<b>Height</b>	111mm
<b>Dimensions</b>	228.6mm x 149.22mm x 111mm
<b>Width</b>	149.22mm
<b>Weight</b>	3.4kg

## Protection Category

<b>IP Rating</b>	IP56
------------------	------

## Approvals

<b>Standards Met</b>	EN 60529
<b>Compliance/Certifications</b>	CE, RoHS





Size

(See below)

