


MICROWAVE TEST ASSEMBLIES, SMA (male), SMA (male), 50 Ohm, 18 GHz, 1500mm

SF104/11SMA/11SMA/1500mm

Properties

- Applicable up to 18 GHz
- Excellent insertion and return loss
- Extremely reliable and robust
- A wide range of cables, connectors and armours
- MIL qualified



Product configuration	
Type of cable	SUCOFLEX_104
Type description connector A	SF_11_SMA-451
Series connector A	SMA, straight - plug
Type description connector B	SF_11_SMA-451
Series connector B	SMA, straight - plug
Length	1500 mm
Length type	REF to REF

Electrical data	
Impedance	50 Ω
Max. operating frequency	18 GHz
Min. return loss	19 dB
VSWR max	1.253
Max. insertion loss	2.03 dB
Signal delay	4.3 ns/m
Propagation velocity	77 %
Min. screening effectiveness	90 dB
Max. screening frequency	18 GHz
Amplitude stability vs. flexure	+/- 0.2 dB

Mechanical data	
Weight	0.13 kg
Cable diameter	5.5 mm
Static bending radius	16 mm

Environmental data	
Operation temperature	-55 °C ... 125 °C

MICROWAVE TEST ASSEMBLIES, SMA (male), SMA (male), 50 Ohm, 18 GHz, 1500mm
SF104/11SMA/11SMA/1500mm

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
84016756	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Comment

The SUCOFLEX 104 high end cable assemblies are designed to provide optimal performance up to 18 GHz where stringent electrical requirements such as in particular stability and low loss, are important.

Ordering information

Item number	Item description
84016756	SF104/11SMA/11SMA/1500mm

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-PI0586 / Date of publication: 10.04.2025 / uncontrolled copy