


Features

- Suitable for all M510 pumps
- Brushless and sensorless
- Small size
- Speed governed
- Speed control pot
- Enable function

RS PRO EQI-M

RS Stock No.: 125-3571



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

EQI CONTROLLER



Product Description

The EQi-M control board is highly efficient, small and lightweight device and can be quickly and easily installed into the smallest spaces, in a vast range of laboratory, prototype and production equipment.

The EQi will accept an input voltage of up to 28v DC. The output from the EQi can be controlled by either the on board speed control pot or from an external 0-4v input. The speed of the pump is 'Governed' above 12v to maintain a constant flow as the back pressure increases. Below 12v the pump speed will decrease as the voltage is lowered.

The EQi is also current limited to the maximum recommended input power of the M510 to prevent damage to the pump.

General Specifications

Туре	EQi Controller	
Input Connection	2 Screw terminal: Up to 28v/GND	
Output Connection	3 Screw terminal: Phase WVU	

Mechanical Specifications

Dimensions	16 x 23 x 57mm	
Weight	15g	

Electrical Specifications

Supply Voltage	6-28v
Maximum Amps (continuous)	6.5
Maximum Amps (Burst)	15

Protection Category

Safety Category Level	S1
IP Rating	IP 20



Approvals

Compliance/Certifications	ISO 9001 Quality Control Standard	
Declarations	TCS Declaration of Conformity - RoHS Directive 2011/65/EU, SVCH,	
	CMRT, 3TG and REACH compliant.	

Similar Products

Stock No.	Brand	Product Name	For Use With
125-3567	RS PRO	EQi-R	Suitable for R404BL pumps
125-3568	RS PRO	EQi-MG1	Suitable for all MGD1000 pumps
125-3569	RS PRO	EQi-MG2	Suitable for all MGD2000 pumps

