

40mm Tower ROGBC Pole

Local distributor code:

403034835 XVC4B5

EAN Code: 3606480032417

Main

Range of product	Harmony XVC4	
Product or component type	Complete pre-wired monolithic tower light	
Beacon or indicator bank unit type	5 illuminated units	
Sound signalling	Without	
Mounting diameter	40 mm	
Component name	XVC	
Device short name	XVC	
Light source	LED steady red LED steady orange LED steady green LED steady blue LED steady clear	
Supply circuit type	AC/DC	

Complementary

Material	Polycarbonate: illuminated unit ABS (acrylonitrile butadiene-styrene): base unit PBT + ABS (UL94HB): top cover SGP (chromium-plated): support tube
Mounting location	On support tube, 17 mm
Product mounting	On support tube, 17 mm
[Us] rated supply voltage	24 V
[Us] rated supply voltage	24 V
Cable cross section	0.33 mm²
AWG gauge	AWG 22
Cable length	600 mm
Marking	CE
[Uimp] rated impulse withstand voltage	0.8 kV
Current consumption	125 mA
Flashing frequency	1 Hz
Net weight	0.58 kg
Height	543.5 mm

Environment

Standards	IEC 61000-6-2 IEC 61000-6-3	
Product certifications	UL	
Protective treatment	TC	
Ambient air temperature for storage	-3570 °C	
Ambient air temperature for operation	-1050 °C	
Electrical shock protection class	Class I conforming to IEC 61140	
Overvoltage category	Class I conforming to IEC 61140	
IP degree of protection	IP23 vertical surface installation conforming to IEC 60529	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.700 cm
Package 1 Width	75.000 cm
Package 1 Length	6.800 cm
Package 1 Weight	622.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	16.500 cm
Package 2 Width	76.500 cm
Package 2 Length	36.000 cm
Package 2 Weight	7.149 kg
Unit Type of Package 3	P06
Number of Units in Package 3	20
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	22.798 kg

Logistical informations

Country of origin

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint		
Total lifecycle Carbon footprint	23	

Use Better

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)

Use Again

○ Repack and remanufacture		
Take-back	No	


XVC4B5

Dimensions Drawings

Pre-assembled and Pre-wired Tower Light with Support Tube Mounting

Dimensions

Below drawing shows the maximum configuration of the product. Select the number of stages according to the product characteristics in order to get **b** dimension.




No. of illuminated units	b Without buzzer (mm)	b Without buzzer (in.)
1 stage	403.50	15.89
2 stages	438.50	17.26
3 stages	473.50	18.64
4 stages	508.50	20.02
5 stages	543.50	21.40

XVC4B5

Mounting and Clearance

Pre-assembled and Pre-wired Tower Light

Support Tube Mounting



XVC4B5

Technical Illustration

Dimensions

