


# SM6404



## Magnetic-inductive flow meter

SMK12GGX50KG/US-100



### Product characteristics

|                              |                                                 |                |
|------------------------------|-------------------------------------------------|----------------|
| Number of inputs and outputs | Number of analogue outputs: 2                   |                |
| Measuring range              | 0.1...25 l/min                                  | 0.03...6.6 gpm |
| Process connection           | threaded connection Rc 1/2 internal thread DN15 |                |

### Application

|                         |                                                                                           |         |
|-------------------------|-------------------------------------------------------------------------------------------|---------|
| Special feature         | Gold-plated contacts                                                                      |         |
| Application             | for industrial applications                                                               |         |
| Media                   | conductive liquids; water; hydrous media                                                  |         |
| Note on media           | conductivity: $\geq 20 \mu\text{S/cm}$<br>viscosity: $< 70 \text{ mm}^2/\text{s}$ (40 °C) |         |
| Medium temperature [°C] | -10...70                                                                                  |         |
| Pressure rating         | 16 bar                                                                                    | 1.6 MPa |

### Electrical data

|                             |                            |  |
|-----------------------------|----------------------------|--|
| Operating voltage [V]       | 20...30 DC; (to SELV/PELV) |  |
| Current consumption [mA]    | 120; (24 V)                |  |
| Protection class            | III                        |  |
| Reverse polarity protection | yes                        |  |
| Power-on delay time [s]     | 5                          |  |
| Measuring principle         | magnetic-inductive         |  |

### Inputs / outputs

|                              |                               |
|------------------------------|-------------------------------|
| Number of inputs and outputs | Number of analogue outputs: 2 |
|------------------------------|-------------------------------|

### Outputs

|                              |                    |
|------------------------------|--------------------|
| Total number of outputs      | 2                  |
| Output signal                | analogue signal    |
| Number of analogue outputs   | 2                  |
| Analogue current output [mA] | 4...20; (scalable) |

# SM6404



## Magnetic-inductive flow meter

SMK12GGX50KG/US-100

|                                   |                                                                                       |                                |
|-----------------------------------|---------------------------------------------------------------------------------------|--------------------------------|
| Max. load                         | [Ω]                                                                                   | 500                            |
| Overload protection               |                                                                                       | yes                            |
| <b>Measuring/setting range</b>    |                                                                                       |                                |
| Measuring range                   | 0.1...25 l/min                                                                        | 0.03...6.6 gpm                 |
| Display range                     | -30...30 l/min                                                                        | -7.92...7.92 gpm               |
| Resolution                        | 0.05 l/min                                                                            | 0.01 gpm                       |
| Analogue start point ASP          | 0...20 l/min                                                                          | 0...5.28 gpm                   |
| Analogue end point AEP            | 5...25 l/min                                                                          | 1.32...6.6 gpm                 |
| In steps of                       | 0.05 l/min                                                                            | 0.01 gpm                       |
| <b>Temperature monitoring</b>     |                                                                                       |                                |
| Measuring range                   | [°C]                                                                                  | -20...80                       |
| Resolution                        | [°C]                                                                                  | 0.2                            |
| Analogue start point              | [°C]                                                                                  | -20...60                       |
| Analogue end point                | [°C]                                                                                  | 0...80                         |
| In steps of                       | [°C]                                                                                  | 0.2                            |
| <b>Accuracy / deviations</b>      |                                                                                       |                                |
| <b>Flow monitoring</b>            |                                                                                       |                                |
| Accuracy (in the measuring range) |                                                                                       | ± (2 % MW + 0,5 % MEW)         |
| Repeatability                     |                                                                                       | ± 0,2 % MEW                    |
| <b>Temperature monitoring</b>     |                                                                                       |                                |
| Accuracy                          | [K]                                                                                   | ± 2,5 (Q > 1 l/min)            |
| <b>Response times</b>             |                                                                                       |                                |
| <b>Flow monitoring</b>            |                                                                                       |                                |
| Response time                     | [s]                                                                                   | 0.15; (dAP = 0, T19)           |
| Damping process value dAP         | [s]                                                                                   | 0...3                          |
| <b>Temperature monitoring</b>     |                                                                                       |                                |
| Dynamic response T05 / T09        | [s]                                                                                   | T09 = 20 (Q > 1 l/min)         |
| <b>Operating conditions</b>       |                                                                                       |                                |
| Ambient temperature               | [°C]                                                                                  | -10...60                       |
| Storage temperature               | [°C]                                                                                  | -25...80                       |
| Protection                        |                                                                                       | IP 67                          |
| <b>Tests / approvals</b>          |                                                                                       |                                |
| EMC                               | DIN EN 60947-5-9                                                                      | 500 V withstand voltage (V DC) |
| CPA approval                      | model number                                                                          | 008MI                          |
|                                   | accuracy class                                                                        | -                              |
|                                   | maximum allowable error                                                               | ± 2,5 % FS                     |
|                                   | Q (min)                                                                               | 0,005 m³/h                     |
|                                   | Q (t)                                                                                 | -                              |
|                                   | Q (max)                                                                               | 1,5 m³/h                       |
| Shock resistance                  | DIN IEC 68-2-27                                                                       | 20 g (11 ms)                   |
| Vibration resistance              | DIN IEC 68-2-6                                                                        | 5 g (10...2000 Hz)             |
| MTTF                              | [years]                                                                               | 175                            |
| UL approval                       | UL Approval no.                                                                       | I011                           |
| Pressure Equipment Directive      | Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request |                                |

# SM6404



## Magnetic-inductive flow meter

SMK12GGX50KG/US-100

| Mechanical data          |      |                                                       |
|--------------------------|------|-------------------------------------------------------|
| Weight                   | [g]  | 515                                                   |
| Housing                  |      | cylindrical                                           |
| Dimensions               | [mm] | Ø 54 / L = 110                                        |
| Materials                |      | stainless steel (316L/1.4404); PBT-GF20; PC; FKM; TPE |
| Materials (wetted parts) |      | stainless steel (316L/1.4404); PEEK; FKM              |
| Process connection       |      | threaded connection Rc 1/2 internal thread DN15       |

| Displays / operating elements |                 |                                                |  |
|-------------------------------|-----------------|------------------------------------------------|--|
| Display                       | Display unit    | 6 x LED, green (l/min, m³/h, gpm, gph, °C, °F) |  |
|                               | measured values | alphanumeric display, 4-digit                  |  |
|                               | programming     | alphanumeric display, 4-digit                  |  |


| Remarks       |                                                                 |
|---------------|-----------------------------------------------------------------|
| Remarks       | MW = measured value<br>MEW = Final value of the measuring range |
| Pack quantity | 1 pcs.                                                          |

### Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



### Connection



OUT1: colours to DIN EN 60947-5-2  
analogue output Temperature monitoring  
OUT2: analogue output volumetric flow quantity monitoring  
Core colours :  
BK = black  
BN = brown  
BU = blue  
WH = white

# SM6404




## Magnetic-inductive flow meter

SMK12GGX50KG/US-100

### Diagrams and graphs

Pressure loss



dP Pressure loss

Q volumetric flow quantity