

9001BF107

control station type B - 1 operator - universal (w/o legend) - stainless plate



Download your 9001BF107 datasheet



Characteristics | Documents & Downloads

Main

 Hide

Range of product	Harmony 9001B
Product or component type	Complete control station
Device short name	9001BF
Control station application	Two functions
Colour of base of enclosure	Grey

Complementary

 Hide

Material	Cast zinc
Marking	CE
Type of operator	Momentary
Control station composition	1 push-button (without marking marking)
Contacts type and composition	1 NO + 1 NC
Mechanical durability	5000000 cycles
Connections - terminals	Screw-clamp terminal
[Ie] rated operational current	5 A at 600 V - utilisation category AC
Device mounting	Flush
Type of installation	Indoor



Environment

 Hide

Ambient air temperature for storage	-40...70 °C
Ambient air temperature for operation	-25...70 °C
NEMA degree of protection	NEMA 1
Product certifications	CSA LR25490 class 3211 03 UL listed file E42259 CCN NKCR

Offer Sustainability

 Hide

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1314 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available  download Product environmental
Product end of life instructions	Available  download End of life manual