


Mini BetaCURVE Thermistor Probe (MBD)



- NTC Temperature Sensor
- Fast time response
- Small tip diameter
- Various lead lengths available

DESCRIPTION

NTC Thermistor soldered to 30 AWG Solid Silver Plated Copper Wire with PVDF Insulation. Unit is potted in a polyimide tube with thermally conductive black epoxy.

FEATURES

Rapid Time Constant
(400 milliseconds in liquids).
Standards supplied with $\pm 0.2^\circ\text{C}$ tolerance
(0°C to $+70^\circ\text{C}$).
Custom tolerances available on request
Temperature range -40°C to $+125^\circ\text{C}$

APPLICATIONS

Reduced size allows localized
temperature sensing
Small Medical probes
Micro-flow sensing

PERFORMANCE SPECS

Parameters	Units	Value
Nominal Resistance at $+25^\circ\text{C}$	Ohms	10000
Resistance tolerance from 0°C to $+70^\circ\text{C}$	$^\circ\text{C}$	± 0.2
Alpha Value at $+25^\circ\text{C}$	$\%/^\circ\text{C}$	4.39
Beta Value 25/85	K	3976
Tolerance on Beta Value 25/85	%	± 0.5
Time response in Liquids	milliseconds	400
Dissipation Constant in still air	$\text{mW}/^\circ\text{C}$	0.5

Mini BetaCURVE Thermistor Probe (MBD)

MECHANICAL DETAILS




Figure 1: Mini BetaCURVE Thermistor Probe (MBD)

RESISTANCE V TEMPERATURE TABLE

Temp. °C	Ohms	Temp. °C	Ohms	Temp. °C	Ohms	Temp. °C	Ohms
-40	336103.2	-12	61702.9	16	15000.9	44	4541.7
-39	314558.0	-11	58405.5	17	14324.5	45	4367.0
-38	294529.1	-10	55303.9	18	13682.3	46	4200.0
-37	275900.8	-9	52385.2	19	13072.6	47	4040.2
-36	258567.0	-8	49637.8	20	12493.3	48	3887.4
-35	242430.2	-7	47050.6	21	11943.0	49	3741.1
-34	227400.9	-6	44613.4	22	11419.9	50	3601.1
-33	213396.6	-5	42316.7	23	10922.7	51	3467.0
-32	200341.4	-4	40151.6	24	10449.8	52	3338.7
-31	188165.5	-3	38110.0	25	10000.0	53	3215.8
-30	176804.8	-2	36184.0	26	9572.0	54	3098.0
-29	166199.8	-1	34366.6	27	9164.7	55	2985.2
-28	156296.1	0	32650.9	28	8777.0	56	2877.0
-27	147043.2	1	31030.8	29	8407.7	57	2773.3
-26	138394.7	2	29500.5	30	8056.1	58	2673.9
-25	130307.6	3	28054.4	31	7721.0	59	2578.6
-24	122742.3	4	26687.5	32	7401.7	60	2487.1
-23	115662.2	5	25395.0	33	7097.3	61	2399.4
-22	109033.4	6	24172.5	34	6807.1	62	2315.2
-21	102824.6	7	23015.9	35	6530.3	63	2234.4
-20	97006.9	8	21921.2	36	6266.2	64	2156.8
-19	91553.3	9	20884.7	37	6014.3	65	2082.3
-18	86439.2	10	19903.2	38	5773.8	66	2010.8
-17	81641.4	11	18973.3	39	5544.2	67	1942.1
-16	77138.6	12	18092.2	40	5325.0	68	1876.0
-15	72911.1	13	17256.9	41	5115.6	69	1812.6
-14	68940.4	14	16464.9	42	4915.6	70	1751.6
-13	65209.7	15	15713.7	43	4724.4	71	1693.0

Mini BetaCURVE Thermistor Probe (MBD)

72	1636.6	86	1037.3	100	678.4	114	456.5
73	1582.4	87	1005.3	101	658.9	115	444.2
74	1530.2	88	974.4	102	640.0	116	432.3
75	1480.1	89	944.7	103	621.8	117	420.8
76	1431.8	90	916.0	104	604.2	118	409.7
77	1385.3	91	888.3	105	587.1	119	398.8
78	1340.6	92	861.5	106	570.6	120	388.4
79	1297.5	93	835.8	107	554.6	121	378.2
80	1256.1	94	810.9	108	539.2	122	368.3
81	1216.1	95	786.8	109	524.3	123	358.8
82	1177.7	96	763.6	110	509.8	124	349.5
83	1140.6	97	741.2	111	495.9	125	340.6
84	1104.9	98	719.6	112	482.3		
85	1070.5	99	698.6	113	469.2		

ORDERING INFORMATION

Part Number	Description	Ω @25°C	MOQ
10K3MBD1	Mini BetaCurve Thermistor Probe (MBD)	10000	1000 *

* For quantities less than Minimum Order Quantity – contact distribution

NORTH AMERICA

Measurement Specialties, Inc.
910 Turnpike Road
Shrewsbury, MA 01545
Tel: 1-508-842-0516
Fax: 1-508-842-0342
Sales:
temperature.cs.amer@meas-spec.com

EUROPE

Measurement Specialties, Inc
Ballybrit Business Park
Galway Ireland
Tel: +353-91-753238
Fax: +353-91-770789
Sales:
temperature.cs.emea@meas-spec.com

ASIA

Measurement Specialties
(China) Ltd.
No. 26, Langshan Road,
Shenzhen High-tech Park
(North)
Nanshan District, Shenzhen,
China 518057
Sales:
temperature.cs.asia@meas-spec.com

The information in this sheet has been carefully reviewed and is believed to be accurate; however, no responsibility is assumed for inaccuracies. Furthermore, this information does not convey to the purchaser of such devices any license under the patent rights to the manufacturer. Measurement Specialties, Inc. reserves the right to make changes without further notice to any product herein. Measurement Specialties, Inc. makes no warranty, representation or guarantee regarding the suitability of its product for any particular purpose, nor does Measurement Specialties, Inc. assume any liability arising out of the application or use of any product or circuit and specifically disclaims any and all liability, including without limitation consequential or incidental damages. Typical parameters can and do vary in different applications. All operating parameters must be validated for each customer application by customer's technical experts. Measurement Specialties, Inc. does not convey any license under its patent rights nor the rights of others.