

General Information

Extended Product Type:	SKT200-180
Product ID:	7TCA300120R0001
EAN:	5415022210095
Catalog Description:	NATURAL TIE 180N 200MM OEM PACK
Long Description:	Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 200mm (7.87 Inches), Width of 3.6mm (0.142 Inches), Thickness of 1.2mm (0.047 Inches), Tensile Strength Rating of 180 Newtons (40 Pounds), Bulk Pack

Categories

Products » Low Voltage Products and Systems » Protection, Connection & Wire Management » Wire Management and Connectivity » Cable Ties

Ordering

EAN:	5415022210095
Minimum Order Quantity:	1000 piece
Customs Tariff Number:	3926909995

Dimensions

Product Net Weight:	1.089 g
---------------------	---------

Container Information

Package Level 1 Units:	1000 piece
Package Level 1 Width:	350.012 mm
Package Level 1 Height:	70.104 mm
Package Level 1 Length:	379.984 mm
Package Level 2 Units:	22000 piece
Package Level 2 Width:	401.32 mm
Package Level 2 Height:	365.76 mm
Package Level 2 Length:	576.58 mm

Additional Information

Product Main Type:	GENERAL PURPOSE CABLE TIES AND ACCESSORIES
Product Name:	OTHER PLASTIC ITEM
UPC:	753554016361

Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	SKT200-180
------------------------------------	------------

Classifications

ETIM 6:	EC000046 - Cable tie
UNSPSC:	39121703

