





	Clamping width mm	Female thread	Outer Ø mm	Length (closed) mm	Weight kg	Order No.
 <p><b>Futuro Plus H1, R + L quick-action chuck</b></p> <ul style="list-style-type: none"> <li>■ Special design for drills with spindle stop</li> <li>■ Plastic sleeve</li> <li>■ 1-sleeve without supporting ring</li> <li>■ Keyless for quick tool change</li> <li>■ Not impact-proof</li> <li>■ Drills through using locking screw for clockwise and anticlockwise operating machines</li> <li>■ With key surface for assembly and disassembly</li> </ul>	1 - 10	3/8"-24 UNF	42,7	61	0,2	6.36515*
	1 - 10	1/2"-20 UNF	42,7	61	0,2	6.36516*
	1,5 - 13	1/2"-20 UNF	42,7	72,4	0,2	6.36517*

 <p><b>Futuro Plus H1 M, R+L quick-action chuck</b></p> <ul style="list-style-type: none"> <li>■ Special design for drills with spindle stop</li> <li>■ Sturdy design with metal sleeve</li> <li>■ 1-sleeve (without supporting ring)</li> <li>■ Keyless for quick tool change</li> <li>■ Not impact-proof</li> <li>■ With key surface for assembly and disassembly</li> </ul>	0,8 - 6,5	1/2"-20 UNF	34	57	0,14	6.36623*
---	-----------	-------------	----	----	------	----------

**Geared chuck, impact-proof**

	Clamping width mm	Female thread	Outer Ø mm	Length (closed) mm	Weight kg	Order No.
 <p><b>Geared chuck with key, R</b></p> <ul style="list-style-type: none"> <li>■ Tried and tested 1000 times</li> <li>■ The chuck for every type of job</li> <li>■ With female thread or taper socket for stationary or hand-held drills and for hand-held impact drills</li> <li>■ The clamping force remains constant during drilling and impact drilling</li> <li>■ For clockwise rotating drills only</li> </ul>	0,5 - 6,5	3/8"-24 UNF	30	53	0,17	6.35008
	1 - 10	3/8"-24 UNF	33,3	61	0,21	6.35019
	1 - 10	1/2"-20 UNF	33,3	61	0,2	6.35072
	1,5 - 13	3/8"-24 UNF	42,5	74	0,32	6.35033
	1,5 - 13	1/2"-20 UNF	42,5	74	0,31	6.35035
	1,5 - 13	1/2"-20 UNF	42,5	74	0,31	6.35302*
	1,5 - 13	B16	42,5	78	0,35	6.35036
	3 - 16	1/2"-20 UNF	50	87,5	0,6	6.35054
	3 - 16	5/8" - 16 UN	50	87,5	0,59	6.35056
	3 - 16	B16	50	86	0,64	6.35050
	3 - 16	B18	50	94,5	0,63	6.35049
	5 - 20	B22	65	113	0,75	6.35058

 <p><b>Geared chuck with key, R + L</b></p> <ul style="list-style-type: none"> <li>■ Tried and tested 1000 times</li> <li>■ The chuck for every type of job</li> <li>■ With female thread or taper socket for stationary or hand-held drills and for hand-held impact drills</li> <li>■ The clamping force remains constant during drilling and impact drilling</li> <li>■ Drills through using locking screw for clockwise and anticlockwise operating machines</li> </ul>	1 - 10	3/8"-24 UNF	33,3	61	0,17	6.35254
	1 - 10	1/2"-20 UNF	33,3	61	0,17	6.35252
	1,5 - 13	3/8"-24 UNF	42,5	74	0,31	6.35255
	1,5 - 13	1/2"-20 UNF	42,5	74	0,31	6.35250
	3 - 16	5/8" - 16 UN	50	87,5	0,6	6.35253
	1,5 - 13	1/2"-20 UNF	42,5	74	0,32	6.35304*

DRILLING/  
SCREWDRIVING

METAL PROCESSING

SAWING

GRINDING/ROUTING/  
PLANING

ACCESSORIES FOR  
SPECIAL TOOLS

WOOD PROCESSING,  
SEMI-STATIONARY

WATER/PUMP  
TECHNOLOGY

ACCESSORIES FOR  
PNEUMATIC TOOLS