



FAG

6044-M-C3

Deep groove ball bearing

Deep groove ball bearing 60...-M, single row,
solid brass cage

Technical information



Your current product variant

Sealing	Without	Not sealed
Cage	M	Solid brass cage, rolling element guided
Tolerance class	PN	Normal (PN)
Dimensional / heat stabilization	S1	Rings dimensional stabilized up to 200°
Lubricant	Without	Bearing not greased
Radial internal clearance	C3 (Group 3)	Internal clearance larger than CN
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	220 mm	Bore diameter
D	340 mm	Outside diameter
B	56 mm	Width
C _r	247,000 N	Basic dynamic load rating, radial
C _{0r}	290,000 N	Basic static load rating, radial
C _{ur}	11,500 N	Fatigue load limit, radial
n _G	3,300 1/min	Limiting speed
n _{gr}	2,700 1/min	Reference speed
≈m	18.7 kg	Weight



Mounting dimensions

$d_{a\ min}$	232.4 mm	Minimum diameter shaft shoulder
$D_{a\ max}$	327.6 mm	Maximum diameter of housing shoulder
$r_{a\ max}$	2.5 mm	Maximum fillet radius

Dimensions

$r_{\ min}$	3 mm	Minimum chamfer dimension
$D_{\ 1}$	303.05 mm	Shoulder diameter outer ring
$d_{\ 1}$	258.05 mm	Shoulder diameter inner ring

Temperature range

$T_{\ min}$	-30 °C	Operating temperature min.
$T_{\ max}$	200 °C	Operating temperature max.

Calculation factors

$f_{\ 0}$	15.5	Calculation factor
-----------	------	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Grease Lubrication
	Oil Lubrication
	Not sealed
	Large bearing