


TIMKEN

The Timken Company
 4500 Mt Pleasant St. NW
 N. Canton, OH 44720
 Phone: (234) 262-3000
 E-Mail: CustomerCAD@timken.com • Web site: www.timken.com

Timken Part Number LM300849 - LM300811, Tapered Roller Bearings - TS (Tapered Single) Imperial

This is the most basic and most widely used type of tapered roller bearing. It consists of two main separable parts: the cone (inner ring) assembly and the cup (outer ring). It is typically mounted in opposing pairs on a shaft.



[Specifications](#) | [Dimensions](#) | [Abutment and Fillet Dimensions](#) | [Basic Load Ratings](#) | [Factors](#)

Specifications

Series	LM300800
Cone Part Number	LM300849
Cup Part Number	LM300811
Design Units	Imperial
Bearing Weight	0.50 lb 0.200 Kg
Cage Type	Stamped Steel

Dimensions

d - Bore	1.6137 in 40.988 mm
D - Cup Outer Diameter	2.6762 in 67.975 mm

B - Cone Width	0.7087 in 18.001 mm
C - Cup Width	0.5315 in 13.500 mm
T - Bearing Width	0.6890 in 17.501 mm

Abutment and Fillet Dimensions

R - Cone Backface "To Clear" Radius¹	0.14 in 3.560 mm
r - Cup Backface "To Clear" Radius²	0.060 in 1.52 mm
da - Cone Frontface Backing Diameter	1.79 in 45.47 mm
db - Cone Backface Backing Diameter	2.05 in 52.07 mm
Da - Cup Frontface Backing Diameter	2.60 in 66.00 mm
Db - Cup Backface Backing Diameter	2.40 in 60.96 mm
Ab - Cage-Cone Frontface Clearance	0.08 in 2 mm
Aa - Cage-Cone Backface Clearance	0.01 in 0.3 mm
a - Effective Center Location³	-0.14 in -3.60 mm

Basic Load Ratings

C90 - Dynamic Radial Rating (90 million revolutions)⁴	3440 lbf 15300 N
C1 - Dynamic Radial Rating (1 million revolutions)⁵	13300 lbf 59100 N
C0 - Static Radial Rating	14300 lbf 63500 N
C_{a90} - Dynamic Thrust Rating (90 million revolutions)⁶	2050 lbf 9140 N

Factors

K - Factor⁷	1.68
e - ISO Factor⁸	0.35
Y - ISO Factor⁹	1.72
G1 - Heat Generation Factor (Roller-Raceway)	22.5
G2 - Heat Generation Factor (Rib-Roller End)	18.1
Cg - Geometry Factor	0.0698

¹ These maximum fillet radii will be cleared by the bearing corners.

² These maximum fillet radii will be cleared by the bearing corners.

³ Negative value indicates effective center inside cone backface.

⁴ Based on 90×10^6 revolutions L_{10} life, for The Timken Company life calculation method. C_{90} and C_{a90} are radial and thrust values.


⁵ Based on 1×10^6 revolutions L_{10} life, for the ISO life calculation method.

⁶ Based on 90×10^6 revolutions L_{10} life, for The Timken Company life calculation method. C_{90} and C_{a90} are radial and thrust values for a single-row, $C_{90(2)}$ is the two-row radial value.

⁷ These factors apply for both inch and metric calculations. Consult your Timken representative for instruction on use.

⁸ These factors apply for both inch and metric calculations. Consult your Timken representative for instruction on use.

⁹ These factors apply for both inch and metric calculations. Consult your Timken representative for instruction on use.



IMPERIAL UNITS

ISO Factor - e	0.35
ISO Factor - Y	1.72
Bearing Weight	0.5 lb
Number of Rollers Per Row	22
Effective Center Location	-0.14 inch



**LM300849 - LM300811
TS BEARING ASSEMBLY**

THE TIMKEN COMPANY
NORTH CANTON, OHIO USA

K Factor	1.68
Dynamic Radial Rating - C90	3440 lbf
Dynamic Thrust Rating - Ca90	2050 lbf
Static Radial Rating - C0	14300 lbf
Dynamic Radial Rating - C1	13300 lbf

Every reasonable effort has been made to ensure the accuracy of the information contained in this writing, but no liability is accepted for errors, omissions or for any other reason.

FOR DISCUSSION ONLY