



Main

Range	New Unica
Product or component type	TV/FM socket
Device application	Communication Media device support
Device presentation	Mechanism
TV socket type	Individual
Colour tint	Anthracite (RAL 7021)

Complementary

TV connector	Male IEC 9.52 mm
Radio connector	Female IEC 9.52 mm
Path attenuation	11 DB TV/VHF signal47...75 MHz 11 DB TV/UHF signal170...862 MHz 11 dB R signal88...110 MHz
DC current flow	No
Number of modules	2 modules
Material	Thermoplastic ABS-UV stabilised: central plate
Surface finish	Painted powder coated
Marking	With imprint
Device mounting	Flush
Fixing mode	Clip-in
Depth	28 mm
Width	45 mm
Height	45 mm
Embedding depth	18 mm
Net weight	0.073 kg
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

IP degree of protection	IP20
IK degree of protection	IK01
Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-25...55 °C
Standards	CE

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Minimum percentage of recycled plastic content	5