




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.51 – 1.31 mm²**

Mating Tab Width: **4.75 mm [.187 in]**

Mating Tab Thickness: **.51 mm [.02 in]**

Features

Product Type Features

Insertion Force	Normal
-----------------	--------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	4.75 mm[.187 in]
Mating Tab Thickness	.51 mm[.02 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	Tab-Lok
Barrel Type	Open

Termination Features

--	--



Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

	.035 in
Wire Insulation Support	With
Mating Retention Type	Dimple

Dimensions

Product Length	13.46 mm[.53 in]
Compatible Insulation Diameter Range	2.79 – 4.32 mm[.11 – .17 in]
Terminal Material Thickness	.3 mm[.012 in]
Wire Size	.51 – 1.31 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
---	---------

Packaging Features

Packaging Quantity	6000
Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer




This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1855568-1 HDM/FA EAPRHB.140 TAB LOC.1400 BCH G CUT	 TE Part # 60755-1 187 FASTON FLAG REC 20-16 AWG BR	 TE Part # 60755-2 187 FASTON FLAG REC 20-16 AWG TPBR	 TE Part # 1-42800-2 187 FASTON,REC.,16-20 AWG,TPBR
--	---	--	--

Also in the Series | FASTON 187

 Crimp Terminal Housings(40)	 Insertion & Extraction Tools(1)	 Insulation Boots & Sleeves(1)	 Joints & Splices(1)
 PCB Terminals(42)	 Quick Disconnects(205)	 Splices(1)	

Customers Also Bought



TE Part #1-2232263-3
PTL 1X4 CAP PANEL MT HOT WIRE
KEYA BLK

TE Part #1217073-1
CONT AMVAR 125 BLADE 020 TPBR

TE Part #180388-2
250 FASTON,REC.,20-16 AWG,TPBR

TE Part #293011-1
5 POS. FASTIN-FASTON CONN. TAB
HOUSING R

TE Part #1376395-1
5MM POWER KEY D/L PLATE GREEN

TE Part #1217071-1
CONTACT, BLADE 125 20-16 AWG
TPBR

TE Part #1971784-2
PTL TAB CONTACT, 16-19 AWG, 2X22
AWG

TE Part #1241857-5
5 POS FASTIN/ON HOUSING PANEL
MOUNT

TE Part #1394429-6
TP 1394429-2 wh 2-703453-0 PP no Ni
PLTN

TE Part #2-1971777-4
PTL TPA HWI 1X4 NATURAL

Documents

Product Drawings

187 FASTON REC 20-16 AWG TPBR

English

CAD Files

Customer View Model

ENG_CVM_CVM_42800-2_BZ.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_42800-2_BZ.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_42800-2_BZ.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



82004 FASTON Terminals (Insulated and Uninsulated) Catalog - FASTON Receptacles Section

English

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English