

Indoor IP Compact IR 720p

Art. no. TVIP91100

Page 1 of 3



- HD 720p resolution: 1280 x 720 @ 25 fps
- 3.6 mm fixed lens
- Day/night switching with electromechanical IR swivel filter (ICR)
- IR LEDs for night vision
- DWDR function to compensate for image contrasts
- Power over Ethernet (PoE)
- ONVIF compatible

Excellent HD image quality

This IP compact camera provides high image quality in 720p HD resolution at a rate of 25 images per second, as well as a variety of functions for professional yet cost-effective surveillance. With its 3.6 mm fixed lens and angle of view of 80°, the camera is ideal for securing offices, businesses or banks.

The integrated infrared LEDs ensure consistently high quality of the image data in darkness and eliminate the need for additional external lighting or other IR illuminators at ranges up to 10 metres to the monitored area (depending on environmental conditions).

IP surveillance camera for indoor use

Thanks to its compact size of 75 x 75 x 145 mm, it is one of the smallest IP camera in the ABUS range and is especially designed for indoor surveillance. With the indoor compact camera, ABUS provides an excellent, modern design that sets new trends in video surveillance.

Easy setup and innovative user management

The practical installation wizard ensures quick and easy setup of the camera. Innovative user management also facilitates user authorisation configuration that is tailored to your security needs. Thanks to Power over Ethernet (PoE), the compact camera can be supplied with power via the Ethernet cable.

The complete ABUS IP camera range in its timeless ABUS design, with fitting ABUS recorder data storage options and video management software data storage solution, entire projects can be implemented to exact standards

Indoor IP Compact IR 720p

Art. no. TVIP91100

Page 2 of 3

with high-quality components all from a single source.

Note: the camera does not have a power supply unit because it can be supplied with power via PoE.

Indoor IP Compact IR 720p

Art. no. TVIP91100

Page 3 of 3

Technical Data:

ONVIF	Profile S
Dimensions	LxBxH (145x82x82) mm
Alarm input (NO/NC)	1
Alarming	Relay, E-Mail
Connections	1 x RJ45, 1 x DC, 1 x Alarm input, 1 x Alarm output
Number of users	10
Number of streams	3
Resolution modes	720p, VGA, CIF pixel
Image sensor	1/4" Progressive Scan CMOS
Pixels (effective)	1280(H) x 800(V) pixel
Frame rate	2, 5, 10, 15, 25 fps
Width	82 mm
Focal length	3,6 mm
Dynamic range (WDR)	46 dB
Electronic shutter	1/25 s - 1/10000 s
Backlight compensation	BLC, DWDR
Height	82 mm
Horizontal angle of view	80 °
IR LEDs	3 (High-Power), 850 nm
IR range	10 m
Compatible with	ABUS VMS, NVR, HDVR, Hybrid DVR
Length	145 mm
Max. resolution @ frame rate	1280 x 720 @ 25 fps
Max. operating temperature	50 °C
Max. humidity	75 %
Microphone	Yes
Min. operating temperature	-10 °C
Minimum illumination (color)	0.5

Minimum illumination (IR)	0
Minimum illumination (B/W)	0,1
Video network bandwidth	32 kBit/s - 8 MBit/s
Network access	RJ45
LAN network access	RJ45
Network camera protocols	IPv4, HTTP, HTTPS, SMTP, UPnP, DNS, DDNS, NTP, RTSP, RTP, TCP, UDP, DHCP, ABUS Server
PoE	IEEE 802.3af
Private zones	3
Noise reduction	2D DNR, 3D DNR
Relay output	1
IP protection class	24
DC voltage supply	12 (+/-10 %) V
Language of instructions	DE, UK, FR, NL, DK, ES, IT, PL, RU
OSD language	DE, UK, FR, NL, DK, ES, IT, PL, RU
Power consumption	270 mA
Day/night switching	ICR/Color/B/W
Supported browsers	IE10, IE11
Encryption	HTTPS
Video compression	H.264, MJPEG
Video system	IP
White balance	AWB
Certifications	CE, C-Tick, RoHS, Reach