



Connectors > Contacts > Connector Contacts > DYNAMIC 3000 CONTACT



Contact Type: **Tab**

Contact Mating Area Plating Material: **Tin (Sn)**

Wire Size: **1.23 – 2.27 mm²**

Product Terminates To: **Wire & Cable**

[All DYNAMIC 3000 CONTACT \(91\)](#)

Features

Contact Features

Mating Tab Thickness	.64 mm[.025 in]
Mating Tab Width	2 mm[.08 in]
Contact Type	Tab
Contact Mating Area Plating Material	Tin (Sn)
Contact Current Rating (Max)	15 A

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Dimensions

Wire Size	1.23 – 2.27 mm ²
-----------	-----------------------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------



Packaging Features

Packaging Method	Reel & Box
------------------	------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 234168-1
EXTRACTION TOOL(DYNAMIC D-3)



TE Part # 2255149-1
MINI SAHT D3000-3L



TE Part # CAT-D9934-A75B
Receptacle and Tab Housing: 5.08 mm Pitch, 250-600V



TE Part # 91561-1
CCII D-3 3L REC TAB 16-14 ASSY



TE Part # CAT-D9934-A75A
DYNAMIC 3100 REC AND TAB HSG

TE Part # CAT-D9934-A75C
DYNAMIC 3500 REC AND TAB HSG

Also in the Series | Dynamic 3000 Series

Connector Contacts(94)

Connector Hardware(8)

Insertion & Extraction Tools(2)

PCB Headers & Receptacles(290)

PCB Terminal Blocks(27)

Power Contacts(94)

Rectangular Power Connectors(386)

Wire-to-Board Headers & Receptacles (290)

Customers Also Bought

TE Part #CAT-EC7491-T273
Econoseal Receptacles and Tabs

TE Part #178289-3
3.81 DYNAMIC REC HSG 6P D--D

TE Part #2822354-1
070 TYPE RUBBER PLUG

TE Part #CAT-D9934-A75
DYNAMIC 3000 CONTACT

TE Part #1-174355-1
E-J MK-2 CAP HSG 2P NATURAL

TE Part #1-179552-2
DYNAMIC D-3200S TAB HSG 2P K/X

TE Part #T4141042051-000
M12,REAR MOUNTING,FEMALE,A CODE,5P

TE Part #T4140042051-000
M12,REAR MOUNT,MALE,A,5P, SOLDER PCB



Documents

Product Drawings

DYNAMIC D-3 TAB CONT. 3L PRE-TIN

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_353716-5_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_353716-5_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_353716-5_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (non U.S.)

English

Agency Approvals

TUV Certificate

English