

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUL 2017 (174) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #T4140412051-000
M12,REAR MOUNTING,MALE,B
CODE,5P



TE Part #1-1437464-7
SCFRX902AA=TIMER 10 AMPERES 12



TE Part #02351008-000
GA-HD GCD-SE-500 ASSY



TE Part #1423160-4
7014AD=RLY,STD,ON,4P,120VAC,10





TE Part #1-1625893-1
5W SM M/OX 2% 15R




TE Part #747844-2
09 MSFL RCPT RA 318 (FM,BL)




TE Part #745783-4
25 MSFL RCPT RA 318 (IN,FM)



TE Part #5211511-1
8 CIRC DIN RCPT GRND CLIP



TE Part #480142-2
HSG AMP LEAF 22 POS



TE Part #04-0760-0005
PT101-0010-111-1110

Documents

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_1103071-1_A3.3d_igs.zip

English

Customer View Model

ENG_CVM_1103071-1_A3.3d_stp.zip

English

Customer View Model

ENG_CVM_1103071-1_A3.2d_dxf.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals

UL Report

English